


SCALE 1:5

PACKAGING NOTES:

- 1. TERMINALS MUST BE SINGLE WRAPPED ON PLASTIC REEL WITH MINIMUM 50 LB. PASSIVATED (NON ABRASIVE) SEPARATING MATERIAL.
- 2. TERMINALS MUST FLOW OFF BOTTOM OF REEL FROM LEFT TO RIGHT WITH INSULATION WINGS FACING OBSERVER AND CRIMP WINGS FACING UPWARD.
- 3. PARTS SHOULD BE PLACED IN CLEAN PLASTIC TUBS OR PANS LINED WITH POLYETHYLENE BAGS DURING PROCESSING. BAGS SHALL BE CLOSED DURING STORAGE AND SHIPMENT. NOTE: WAX LINED BOXES MAY BE SUBSTITUTED FOR POLYETHYLENE BAGS. REELS TO BE PROTECTED FROM SHIPPING DAMAGE.










SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.		
TOTAL NO OF INSPECTIONS REQUIRED	22	
LAST NO. USED	13	

MISSING SYMBOLS					DWG STATUS		ZONE	REVISION HISTORY	AUTH	DR
	DATE	STG	REV	N/P	CHG					
NO MISSING SYMBOL NUMBER	09SE09	R	01	-	-		13675583-WAS PE155695; 13675584-WAS PE155694; 13675585-WAS PE155180; ALL PARTS-RELEASED	408836	FR	
	20AU10	R	02	-	-		ALL PARTS - DIM 4.6 +0.1/-0.25 WAS 4.6	411645	HRS	
	16MY11	R	03	-	-		ALL PARTS - 4.45 WAS 4.6 AND 4.6 +0.1/-0.5 WAS 4.6 +0.1/-0.25	414250	JCR	

NOTES

- 1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- 2. REFERENCE MATING COMPONENTS OR EQUIVALENT:
TERMINAL 13675579
- 3. DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE INSERT OR ANY MOVING PART) OF THIS TERMINAL ASSEMBLY. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
- 4. "*" DENOTES DIMENSIONS MADE AT CUT-OFF AND CRIMP DIE.
- 5. RECOMMENDED MAXIMUM CURRENT CAPACITY IS 120 AMPS.
- 6. THESE PARTS ASSEMBLE WITH CONNECTOR ASSEMBLIES SHOWN ON TAXI 13675497 OR EQUIVALENT



REV	N/P	STATUS	TERMINAL	TERMINAL INSERT	SIZE (MM²)	ID	DIAMETER	CONNECTOR MATE DIRECTION	(B2)
01	AB	-	13675573	13675562	8 TO 10	8	4.54 - 5.79	IN-LINE	11.26
01	AB	-	13675574	13675562	13 TO 16	6	6.63 - 8.13	IN-LINE	13.15
01	AB	-	13675575	13675562	19 TO 25	4	7.75 - 10.2	IN-LINE	15.49

PROCESS SENSITIVE DIMENSION			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)	CHART	D	
FROM 0 TO 12	>12		
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.1	±0.2		
ANGULAR TOLERANCE 22°			

3

DWG TYPE PART DRAWING

STYLE

VOLUME (CM³) DISTR CODE D

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 3D GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE SHOWN SEPARATELY REGARDLESS OF DATUM REFERENCES.

ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

NX

DELPHI

DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
WARREN, OH

DR

APV01 FAVIOLA RAMON 09

APV02 J. VILLAMIL 15

APV03 ROBERTO HINOJOSA 18

APV04

APV05

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001

MATERIAL SEE DRAWING

DRAWING NAME TAXI ASM TERM F PWR PACK 1000 AG SEALED

DRAWING NUMBER 13675580

SIZE A1 SCALE 2:1 FRAME NO 1 OF 1 SHEET NO 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13675583](#)