




SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	
	LAST NO. USED		
	18		
	17		





TYPE 401
BLANK VIEW (APPROX)



TYPE 402
BLANK VIEW (APPROX)
SAME AS TYPE 401
EXCEPT AS SHOWN



TYPE 403
BLANK VIEW (APPROX)
SAME AS TYPE 401
EXCEPT AS SHOWN





NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

12048459	CA	-		.0403 X 1.062	M3614155					5.0 - 3.0	4.48 - 3.49	11	401	.204 ±.003	.230	-	-	-					
12048426	BA	-			12048459					5.0 - 3.0	4.48 - 3.49	11	401	(.204)	-	60°	.106	.067					
12010299	CA	-		.0320 X 1.062	M3614129					2.0 - 1.0	3.05 - 2.48	15	401	.345 ±.003	.150	-	-	-					
08917970	FA	-		.0320 X .969	M3614126					2.0 - 1.0	3.34 - 2.84	15	403	.173 ±.003	.150	-	-	-					
08917959	FA	-		.0320 X .969	M3614126	12015038	C	-	OBSOLETE	(TWO) 2.0 - 1.0	3.34 - 2.84	215	403	.173 ±.003	.225	-	-	-					
06288749	CK	-	OBSOLETE	.0320 X 1.062	M3614129					2.0 - 1.0	3.05 - 2.48	15	401	.282 ±.003	.150	-	-	-					
06288591	BH	-	OBSOLETE	.0403 X 1.062	M1403155					5.0 - 3.0	4.48 - 3.49	11	401	.204 ±.003	.230	-	-	-					
02989600	CK	-	OBSOLETE	.0320 X .844	M3614123	02989601	CK	-	OBSOLETE	5.0 - 3.0	-	11	402	.204 ±.003	.315	-	-	-					
02989521	CM	-		.0320 X 1.062	M3614129	02989522	CM	-	OBSOLETE	0.5 - 0.8	2.40 - 2.03	19	401	.345 ±.003	.145	-	-	-					
02984145	BK	-	OBSOLETE	.0320 X .844	M3614123	02965711	BK	-	OBSOLETE	5.0 - 3.0	-	11	402	.345 ±.003	.315	-	-	-					
02984144	BK	-	OBSOLETE	.0320 X .844	M3614123	02965645	BK	-	OBSOLETE	5.0 - 3.0	-	11	402	.282 ±.003	.315	-	-	-					
02977489	BL	-		.0403 X 1.062	M3614155					5.0 - 3.0	4.48 - 3.49	11	401	.235 ±.003	.230	-	-	-					
02965614	BL	-		.0403 X 1.062	M3614155	06288634	BM	-		5.0 - 3.0	4.48 - 3.49	11	401	.282 ±.003	.230	-	-	-					
PART	NO	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC	PART	NO	REV	N/P	STATUS	MAT'L SPEC	SIZE (MM²)	DIA (MM)	ID	TYPE	A ±.003	G ±.015	V ±5°	W±0.03	X±0.03		
UNPLATED						TIN PLATED						CABLE											

.345	5/16	MB
.282	1/4	M6.3
.235	#12	
.204	#10	M5
.173	#8	M4
Ø A ±.003	STANDARD	METRIC
	SCREW/STUD SIZE	

PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE RETROFIT DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (IN)	CHART
FROM 0	>500
TO .500	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±.005	±.010
ANGULAR TOLERANCE ±2°	



DWG TYPE: PART DRAWING

STYLE: _____

VOLUME (CM³): _____

ROUTING: 6900

UNLESS OTHERWISE SPECIFIED: THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 ADDENDUM. DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNING OF FEATURES MAY BE GIVEN SEPARATELY REGARDLESS OF REFERENCES.

ALL DIMENSIONS ARE IN INCHES

REFERENCE: _____

DELPHI

DELPHI PACKARD ELECTRIC SYSTEMS
WARREN, OH

DR: _____ DATE: _____

APVD1: JOSE LUIS TAPIA 04MR04

APVD2: FRANCISCO KOPKA 04MR04

APVD3: ERIC HAROLDSON 05MR04

APVD4: _____

APVD5: _____

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001

MATERIAL SEC. CHART

DRAWING NAME: TAXI TERM RING STR

DRAWING NUMBER: 02962869

SIZE: A0 SCALE: 5:1 FRAME NO: 1 SHEET NO: 4 OF 4 STG: R REV: 01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[02965614](#) [02989521](#) [06288634](#)