



SYMBOL DEFINITION			MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	13	1-2,6-9,17-20,	
	LAST NO. USED	28		

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR
DATE	STG	REV	N/P	CHG				
29NO99	R	01	-	-		CLEARED REV COLUMN AND 15355365 - WAS PE080104 AND RELEASED	990005	AM
08FE00	R	02	-	-		TOLERANCE SYMBOLS - REVISED, NOTES - REVISED, OPTIONAL CONSTRUCTION - CLARIFIED, DIMENSIONS - REVISED	198080	JEE
07AU01	R	03	-	-		ALL PARTS - ADDED 0.06; UPDATED PDM ATTRIBUTES; REVISED NOTES; REMOVED OPTIONAL CONSTRUCTION	212463	TSH
12NO03	R	04	-	-		ALL PARTS - ADDED NOTES 586 AND REVISED MATERIAL SPECS	248441	HAM
23OC18	R	05	-	-		ALL PARTS - UPDATED DESIGN & ENGINEERING CONTROL AND ADDED NOTE	441287	LVD

THE DESIGN AND ENGINEERING CONTROL OF THIS COMPONENT HAS BEEN TRANSFERRED TO APTIV/HELLERMANNTYTON

- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - RECOMMENDED HOLE SIZE FOR CLIP .25 ± .01 DIA HOLE IN .15 MAX THICK STOCK.
 - THIS PART TO FIT .406 OR .493 ID CONVOLUTED CONDUIT.
 - DIMENSIONS MARKED WITH ● MAY VARY -.025 DUE TO BOW.
 - MATERIAL RECYCLING CODE PER ISO 11469. (11X10.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
 - CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER THE LATEST REVISION OF ESD S1085201.

15355365	01	AD	POLYPROPYLENE COMPOUND NATURAL	1.504
15358683	A4	-	POLYPROPYLENE COMPOUND GRAY	1.504
08905794	H9	-	POLYPROPYLENE COMPOUND BLACK	1.504
PART NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	VOL CM³

(21) PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (IN)	CHART H
FROM 0 TO .750	>1.250
TO .750 TO 1.250	>2.500
1.250 TO 2.500	>4.000
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±.005	±.010
±.010	±.015
±.015	±.020
ANGULAR TOLERANCE ±.2°	

LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.

DWG TYPE: PART DRAWING

STYLE: SEE CHART

VOLUME (CM³): SEE CHART

DISTR CODE: D

UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2003 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2003. SEPARATE PATTERNS OF FEATURES MAY BE SHOWN SEPARATELY, RESPECTIVE OF DATUM REFERENCES.

ALL DIMENSIONS ARE IN INCHES

REFERENCE:

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

NX

• APTIV •

CONNECTION SYSTEMS

WARREN, OH

COPYRIGHT 1998 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION, OR UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA FOR ANY PURPOSE WITHOUT THE WRITTEN AUTHORIZATION OF APTIV IS PROHIBITED.

DR	
APV01	P. H. CASTRILLON
APV02	R. RAMOS S.
APV03	E. TRACEY
APV04	
APV05	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001

MATERIAL SEE CHART

DRAWING NAME: TAXI MOUN CLIP CDT 10/13MM RO

DRAWING NUMBER: 15355170

SIZE	SCALE	FRAME NO	SHEET NO	SYT
A1	5:1	1 OF 1	1 OF 1	R

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[08905794](#)