






SYMBOL DEFINITION			MISSING NUMBERS
THE NUMBER INSIDE THE SYMBOL  CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	13	
	LAST NO. USED	13	

DWG STATUS					ZONE	REVISION HISTORY			AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG								
25N099	R	01	-	-			ALL PARTS - REDRAWN TO PD			196858	CMP	GMC DN
170C01	R	02	-	-			ALL PARTS - ADDED OPTIONAL CONSTRUCTION & MATERIAL RECYCLING CODE NOTES & REVISED CAVITIES ID LOCATIONS			215985	EOV	EOV GMC
04SE02	R	03	-	-			ALL PARTS - SECONDARY TERMINAL LOCK NOTE WAS 12047664			230019	RVP	RVP GMC
23N005	R	04	-	-			ALL PARTS - ADDED NOTE 7			274632	BB	BB BG
30MR06	R	05	-	-			12059249 - MAT'L SPEC WAS M3592002			278565	GPS	FRG JGS




NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR SEE CHART
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 12047883
MAX INSULATION CRIMP MUST BE LESS THAN 2.3 HIGH AND 2.7 WIDE.
SECONDARY TERMINAL LOCK 15324070
- (2.3)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.
- FOR MATING CONFIGURATION REQUIREMENTS, SEE PART NUMBER 13548762.

12059249	02	-	-	M3592024 PA66 HS IM CRM	12059250	0.583
12059247	A4	-	-	M3592025 PA66 HS IM GRA MD	12059248	0.583
12047662	A5	-	-	M3592001 PA66 HS IM BLK	12047663	0.583
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	MATING CONNECTOR	VOLUME CM³

(13) PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

DIMENSIONAL RANGE (MM)												CHART ET
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300			
TO	20	30	70	100	150	200	250	300	400			
TOLERANCE UNLESS OTHERWISE SPECIFIED												
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2												
ANGULAR TOLERANCE #2°												

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)		DISTR CODE	
SEE CHART		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
		USE MATH DATA	
			

DELPHI						
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH						
DR					DATE	
APVD1	C.MIRANDA				25N099	
APVD2	G.MACIAS				20JA00	
APVD3	D.NAVARRO				26JA00	
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001						
MATERIAL						
SEE CHART						
DRAWING NAME						
TAXI CONN F M/P 150						
DRAWING NUMBER						
12059281						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	05	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12059247](#)