



SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	32
	LAST NO. USED	32


DWG STATUS		ZONE		REVISION HISTORY		AUTH		DR		APVD	
DATE	STG	REV	N/P	CHG							
15MR04	R	06	-	-		ALL PARTS - WERE SEPARATE DWGS AND UPDATED MAT'L SPEC	252884	JVM	JVM	EJH	
16JL04	R	07	-	-		ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES	256676	ESH	FRG	GER	
26A004	R	08	-	-		12089238- OBSOLETE REPLACED BY 12103511	257914	ADK	ADK	GR	






TYPE 201




TYPE 202



TYPE 203
SAME AS TYPE 202
EXCEPT AS SHOWN



TYPE 204
SAME AS TYPE 201
EXCEPT AS SHOWN



TYPE 205
SAME AS TYPE 201
EXCEPT AS SHOWN

						.0403 X 1.250		12103908	A	I				M3649159	8.0	5.54-5.28	8	205	.282±.003	.260	-	-	-	
						.0320 X 1.250		12089562	A		OBSOLETE			M3649134	(2) 1.0 - 0.8	2.70-1.90	217	205	.345±.003	.201	-	-	-	
						.0320 X 1.250		12089238	A	2	OBSOLETE			M3649134	(2) 1.0 - 0.8	2.70-1.90	217	205	.282±.003	.201	-	-	-	
						.0320 X 1.250		12089237	A	I				M3649134	1.0 - 0.8	2.70-1.90	17	205	.282±.003	.142	-	-	-	
						.0320 X 1.250		12084522	A	I				M3649134	3.0 - 2.0	3.70-2.50	13	205	.407±.003	.185	-	-	-	
12048427	B	I					02962953								5.0 - 3.0	4.48-3.39	11	201	(.407)	-	60°	.098	.054	
						.0320 X 1.250		12015910	B	I				M3649134	2.0 - 1.0 & 0.8 - 0.5	3.97 MAX & 3.13 MAX	1519	204	.407±.003	.240	-	-	-	
						.0320 X 1.250		12015909	B	I				M3649134	2.0 - 1.0	3.97 MAX	15	204	.407±.003	.170	-	-	-	
						.0320 X 1.250		12015908	B	I				M3649134	2.0 - 1.0 & 0.8 - 0.5	3.97 MAX & 3.13 MAX	1519	204	.345±.003	.240	-	-	-	
						.0320 X 1.250		12015907	B	I				M3649134	2.0 - 1.0	3.97 MAX	15	204	.345±.003	.170	-	-	-	
						.0320 X 1.172		12015812	C	I				M3649131	(2) 0.8 - 0.5	3.13-2.69	219	203	.407±.003	.160	-	-	-	
						.0320 X 1.172		12015811	C	I				M3649131	(2) 0.8 - 0.5	3.13-2.69	219	203	.345±.003	.160	-	-	-	
12015106	C	I				.0403 X 1.250	M3614159								8.0	5.54-5.28	8	201	.244±.003	.260	-	-	-	
12010836	C	I				.0403 X 1.250	M3614159								8.0	5.54-5.28	8	201	.471±.005	.260	-	-	-	
12010245	C	I				.0403 X 1.250	M3614159								5.0 & 1.0	3.56-3.36	8	201	.345±.003	.280	-	-	-	
12004984	C	I				.0403 X 1.250	M3614159	12010963	C		OBSOLETE			M3649159	8.0	5.54-5.28	8	201	.533±.005	.260	-	-	-	
12004983	C	I				.0403 X 1.250	M3614159	12010047	C		OBSOLETE			M3649159	5.0 - 3.0	4.48-3.49	11	201	.533±.005	.230	-	-	-	
12004483	C	I				.0403 X 1.250	M3614159								2.0 - 1.0	3.97-3.36	15	201	.533±.005	.165	-	-	-	
12004370	B		OBSOLETE			.0403 X 1.250	M3614159								8.0	7.24-6.48	15	201	.407±.003	.260	-	-	-	
12004369	B		OBSOLETE			.0403 X 1.250	M3614159								8.0	7.24-6.48		201	.345±.003	.260	-	-	-	
12004368	B		OBSOLETE			.0403 X 1.250	M3614159								8.0	7.24-6.48		201	.282±.003	.260	-	-	-	
08917796	C	I				.0403 X 1.250	M3614159								5.0 - 3.0	4.48-3.49	11	201	.471±.005	.230	-	-	-	
08917642	C	I				.0403 X 1.250	M3614159	12010822	C		OBSOLETE			M3614159	8.0	5.54-5.28	8	201	.282±.003	.260	-	-	-	
08911809	E		OBSOLETE			.0403 X 1.250	M3614159								8.0	5.54-5.28	8	201	.235±.003	.260	-	-	-	
08911351	E		OBSOLETE			.0403 X 1.250	M3614159								5.0 & 1.0	3.56-3.36	8	201	.204±.003	.280	-	-	-	
06288377	CK		OBSOLETE			.0320 X 1.172	M3614131								2.0 - 1.0	3.05-2.48	15	202	.407±.003	.160	-	-	-	
02989948	CJ		OBSOLETE			.0403 X 1.250	M3614159								8.0	5.54-5.28		201	.407±.003	.260	-	-	-	
02989716	CK	I				.0320 X 1.172	M3614131								(2) 0.8 - 0.5	3.13-2.69	219	202	.345±.003	.160	-	-	-	
02989606	CK	I				.0320 X 1.172	M3614131								0.8 - 0.5	2.40-2.03	19	202	.345±.003	.140	-	-	-	
02984799	CK	I				.0403 X 1.250	M3614159								2.0 - 1.0	3.97-3.36	15	201	.471±.005	.165	-	-	-	
02984756	CK	I				.0320 X 1.172	M3614131								0.8 - 0.5	2.40-2.03	19	202	.407±.003	.140	-	-	-	
02984278	CK		OBSOLETE			.0403 X 1.250	M3614159								(1) 0.8 - (2) 5.0	----		201	.407±.003	.280	-	-	-	
02977493	BK	I				.0403 X 1.250	M3614159	12010821	BK		OBSOLETE			M3649159	2.0 - 1.0	3.97-3.36	15	201	.407±.003	.165	-	-	-	
02977492	BK	I				.0403 X 1.250	M3614159	06294088	BK		OBSOLETE			M3649159	2.0 - 1.0	3.97-3.36	15	201	.345±.003	.165	-	-	-	
02977491	BK	I				.0403 X 1.250	M3614159	12010964	C		OBSOLETE			M3649159	8.0	5.54-5.28	8	201	.345±.003	.260	-	-	-	
02977490	BK	I				.0403 X 1.250	M3614159	02989996	BK		OBSOLETE			M3649159	5.0 - 3.0	4.48-3.49	11	201	.345±.003	.230	-	-	-	
02962976	BK					.0403 X 1.250	M3614159	12010823	BL		OBSOLETE			M3649159	8.0	5.54-5.28	8	201	.407±.003	.260	-	-	-	
02962953	BK	I				.0403 X 1.250	M3614159	02977944	BK		OBSOLETE			M3649159	5.0 - 3.0	4.48-3.49	11	201	.407±.003	.230	-	-	-	
PART NO	REV	N/P	STATUS			MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	STATUS			MAT'L SPEC	SIZE (MM²)	CABLE	DIA (MM)	ID	TYPE	A	G±.015	V±5°	W±.03	X±.03

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[08917642-L](#)