










SYMBOL DEFINITION			MISSING NUMBERS
THE NUMBER INSIDE THE SYMBOL  CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	12	
	LAST NO. USED	12	

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	CK	APVD
DATE	STG	REV	CHG	N/P						
19FE99	R	E4	-	-		REDRAWN TO PD	191576	GEG	GMC	JR



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATING COMPONENTS OR EQUIVALENT: CONNECTOR 12092163
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: TERMINAL 12064971
SECONDARY TERMINAL LOCK 12092164

DELPHI Automotive Systems																																	
MATERIAL SPEC R0071754 PA66 HS 1M - BLK		<table><tr><th colspan="4">DIMENSIONAL RANGE (MM)</th><th>CHART E</th></tr><tr><td>FROM</td><td>0</td><td>> 20</td><td>> 30</td><td>> 70</td></tr><tr><td>TO</td><td>20</td><td>30</td><td>70</td><td>100</td></tr><tr><td colspan="5">TOLERANCE UNLESS OTHERWISE SPECIFIED</td></tr><tr><td colspan="5">[±0.15] ±0.2 ±0.3 ±0.4 ±0.5</td></tr><tr><td colspan="5">ANGULAR TOLERANCE ± 2°</td></tr></table>		DIMENSIONAL RANGE (MM)				CHART E	FROM	0	> 20	> 30	> 70	TO	20	30	70	100	TOLERANCE UNLESS OTHERWISE SPECIFIED					[±0.15] ±0.2 ±0.3 ±0.4 ±0.5					ANGULAR TOLERANCE ± 2°				
DIMENSIONAL RANGE (MM)				CHART E																													
FROM	0	> 20	> 30	> 70																													
TO	20	30	70	100																													
TOLERANCE UNLESS OTHERWISE SPECIFIED																																	
[±0.15] ±0.2 ±0.3 ±0.4 ±0.5																																	
ANGULAR TOLERANCE ± 2°																																	
PART DRAWING				DISTR CODE																													
CODE NUMBER 6900	DWG DATE 120C88	SCALE 5:1																															
QC SPEC -C-4362	STYLE	VOLUME cm³ 1.108																															
PART GEOMETRY 3D SOLID	UNLESS OTHERWISE SPECIFIED: PERFECT FORM REQUIRED FOR FEATURES OF SIZE AT MMC. TRUE POSITION TOLERANCES AND RELATED DATUMS APPLY AT CONDITION OF SIZE INDICATED IN FEATURE CONTROL FRAME. ALL OTHER GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. SEPARATE TRUE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.																																
 CHANGE RESTRICTED NO MANUAL CHANGES	<table><tr><th>REFERENCE</th><th>DR</th><th>DATE</th></tr><tr><td>001,701</td><td>APVD1 GEFF REEVES</td><td>100C88</td></tr><tr><td rowspan="4">COPY OF MATH DATA DO NOT SCALE</td><td>APVD2 TOM NADASKY</td><td>01N088</td></tr><tr><td>APVD3 S. YANG</td><td>22FE89</td></tr><tr><td>APVD4 R. PLYLER</td><td>22FE89</td></tr><tr><td>APVD5</td><td></td></tr></table>				REFERENCE	DR	DATE	001,701	APVD1 GEFF REEVES	100C88	COPY OF MATH DATA DO NOT SCALE	APVD2 TOM NADASKY	01N088	APVD3 S. YANG	22FE89	APVD4 R. PLYLER	22FE89	APVD5															
					REFERENCE	DR	DATE																										
001,701	APVD1 GEFF REEVES	100C88																															
COPY OF MATH DATA DO NOT SCALE	APVD2 TOM NADASKY	01N088																															
	APVD3 S. YANG	22FE89																															
	APVD4 R. PLYLER	22FE89																															
	APVD5																																
METRIC UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS	THIRD ANGLE PROJECTION																																
DRAWING NAME CONN 4F M/P 150		SHEET NUMBER 1 OF 1		DRAWING NUMBER 12092162																													
DWG STATUS STG REV N/P R E4 -		SIZE A1																															

6	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12092162](#)