





D

THIS DRAWING AND DESIGN HEREON CONSTITUTE A PROPRIETARY DESIGN OF PACKARD ELECTRIC DIVISION AND IS NOT TO BE DUPLICATED OR REPRODUCED WITHOUT AUTHORITY OF PACKARD ELECTRIC DIVISION.

DO NOT SCALE

PART NO. 1200 4552

PART NO. 1200 4552



12089823	B		0.406 THK SAE CA 260 BRASS	12010636	▲	F		1	2.0-1.0	3.95	15	4.4
			0.406 THK SAE CA 260 COPPER	12078138	B			1	0.8-0.5	3.10	19	3.2
			0.406 THK SAE CA 260 COPPER	12078136	B			4	2.0-1.0	3.95	15	3.3
12078033	B		0.406 THK SAE CA 260 BRASS					4	5.0-3.0	5.10	11	4.6
12078032	B		0.406 THK SAE CA 260 BRASS	12078137	▲	B		4	3.0	3.20	12	3.3
12078031	B		0.406 THK SAE CA 260 BRASS					4	2.0-1.0	3.95	15	3.3
12066447	A	OBSOLETE	0.406 THK SAE CA 260 BRASS					4	5.0-3.0	5.10	11	4.6
12052443	B		0.406 THK SAE CA 260 BRASS					2	0.8-0.5	3.10	19	3.8
12052209	B		0.406 THK SAE CA 260 BRASS					2	3.0	3.10	12	4.6
12052208	B		0.406 THK SAE CA 260 BRASS					1	3.0	3.10	12	4.6
			0.406 THK SAE CA 195 COPPER	12048293	●	A	OBSOLETE	1	1.0	2.25	16	4.4
			0.406 THK SAE CA 195 COPPER	12048291	●	A		2	0.8-0.5	3.10	19	3.8
			0.406 THK SAE CA 195 COPPER	12048290	●	A		2	2.0-1.0	3.95	15	4.4
			0.406 THK SAE CA 195 COPPER	12048289	●	A	OBSOLETE	2	5.0-3.0	5.10	11	4.6
			0.406 THK SAE CA 195 COPPER	12048281	●	B		1	TWO 2.0-1.0	3.10	215	6.0
			0.406 THK SAE CA 195 COPPER	12048280	●	A	OBSOLETE	1	TWO 0.8-0.5	2.55	219	4.7
			0.406 THK SAE CA 195 COPPER	12048279	●	B		1	TWO 2.0-1.0	3.10	215	6.0
			0.406 THK SAE CA 195 COPPER	12048278	●	B		1	0.8-0.5	3.10	19	3.8
			0.406 THK SAE CA 195 COPPER	12048277	●	B		1	2.0-1.0	3.95	15	4.4
12020400	E		0.406 THK SAE CA 260 BRASS	12089953	B			1	5.0-3.0	5.10	11	4.6
12020338	D		0.406 THK SAE CA 260 BRASS	2010637	▲	E		2	2.0-1.0	3.95	15	4.4
12020337	D		0.406 THK SAE CA 260 BRASS					2	5.0-3.0	5.10	11	4.6
12020336	E		0.406 THK SAE CA 260 BRASS	12089952	B			1	TWO 0.8-0.5	2.55	219	4.7
12020335	E		0.406 THK SAE CA 260 BRASS					1	TWO 2.0-1.0	3.10	215	6.0
12020334	E		0.406 THK SAE CA 260 BRASS	12089951	B			1	0.8-0.5	3.10	19	3.8
12020321	E		0.406 THK SAE CA 260 BRASS	12089950	B			1	2.0-1.0	3.95	15	4.4
12015373	E		0.406 THK SAE CA 260 BRASS					1	0.35-0.22	1.86	23	2.2
12004582	A	OBSOLETE	0.406 THK SAE CA 260 BRASS					3	TWO 0.8-0.5	2.55	219	4.7
12004581	A	OBSOLETE	0.406 THK SAE CA 260 BRASS					3	TWO 2.0-1.0	3.10	215	6.0
12004580	A	OBSOLETE	0.406 THK SAE CA 260 BRASS					3	0.8-0.5	3.10	19	3.1
12004579	A	OBSOLETE	0.406 THK SAE CA 260 BRASS					3	2.0-1.0	3.95	15	3.7
12004578	A	OBSOLETE	0.406 THK SAE CA 260 BRASS					3	5.0-3.0	5.10	11	4.6
12004562	D		0.406 THK SAE CA 260 BRASS					2	TWO 2.0-1.0	3.10	215	6.0
12004561	D		0.406 THK SAE CA 260 BRASS					2	TWO 0.8-0.5	2.55	219	4.7
12004560	E		0.406 THK SAE CA 260 BRASS					2	0.8-0.5	3.10	19	3.8
12004559	E	OBSOLETE	0.406 THK SAE CA 260 BRASS					2	2.0-1.0	3.95	15	4.4
12004558	D	OBSOLETE	0.406 THK SAE CA 260 BRASS					2	5.0-3.0	5.10	11	4.6
12004557	E	OBSOLETE	0.406 THK SAE CA 260 BRASS					1	TWO 0.8-0.5	2.55	219	4.7
12004556	E	OBSOLETE	0.406 THK SAE CA 260 BRASS					1	TWO 2.0-1.0	3.10	215	6.0
12004555	F	OBSOLETE	0.406 THK SAE CA 260 BRASS					1	0.8-0.5	3.10	19	3.8
12004554	F	OBSOLETE	0.406 THK SAE CA 260 BRASS					1	2.0-1.0	3.95	15	4.4
12004553	E	OBSOLETE	0.406 THK SAE CA 260 BRASS					1	5.0-3.0	5.10	11	4.6
PART NO.	REV.	STATUS	MATERIAL	PART NO.	REV.	STATUS	TYPE	SIZE (MM ²)	DIA.	I.D.	A	
			UNPLATED			PLATED					±0.2	

CABLE I.D. NUMBER (AS SPECIFIED IN CHART) IS LOCATED ON UNDERSIDE OF EACH TERMINAL.

■ INDICATES SERRATIONS IN CONDUCTOR WINGS.

▲ INDICATES MATERIAL (C260 ALLOY) IS TIN PLATED OVER COPPER PLATE.

● INDICATES MATERIAL (C195 ALLOY) IS SILVER PLATED OVER NICKEL PLATE.

INDICATES MATERIAL (C260 ALLOY) IS SILVER PLATED OVER NICKEL PLATE.

NOTE — CONTACT PACKARD ELECTRIC SALES DEPARTMENT CONCERNING CURRENT PRODUCT AVAILABILITY.

As of 06JL 90 this drawing is no longer being maintained on computer vision.

CAD CAM (JWP)

METRIC		THIRD ANGLE PROJECTION	
DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED			
CODE NO.	6900	TOLERANCE UNLESS OTHERWISE SPECIFIED	ANGULAR ± 2°
QC		DECIMAL:	ONE PLACE ± 0.3
DATE	07JN78	SCALE	NONE
CD X TERM	12004552.00.01	DR.	
REFERENCE NO.	12004552 "D" SIZE	CK	R. SEBRELL
SHT.	#1, #2, & #6	DATE	03AU84
MATERIAL SPEC.		APPR.	R.D. KEARNS
		DATE	040C84
SEE CHART			
NAME			
TERM F PAC/ON III			
PART NO.	1200 4552	SIZE	D
OUTLINE DRAWING SHEET 1 OF 3			

C05D1974

PACKARD ELECTRIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12048279](#) [12048290](#) [12052443](#) [12048277](#) [12089823](#)