





THE NUMBER INSIDE THE SYMBOL  CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	15	
	LAST NO. USED	17	

[illegible]



CARRIER STRIP VIEW
SCALE 2:1




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



WING CONST I



WING CONST I I



PART NO
1202 0114


Type 101

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. MATING COMPONENTS OR EQUIVALENT:
TERMINAL_12015823

PART NO
1202 0114

PART	NO	REV	STATUS	MAT'L SIZE	MAT'L SPEC	PART NO	REV	STATUS	MAT'L SPEC	SIZE (MM ²)	ID	DIA	TYPE	WING CONST	E _{0.4}
UNPLATED						PLATED				CABLE					
				0.381X42.47		15318040	A1	A2	P3607336 425 TIN BRS 1/2 HD SN PLTD	2-1	15N	3.97-2.48	102	I	3.7
				0.381X42.47		15318039	A1	A2	P3607336 425 TIN BRS 1/2 HD SN PLTD	0.5-0.35	21N	-	101	II	2.4±0.2
				0.381X42.47		15318038	A1	A2	P3607336 425 TIN BRS 1/2 HD SN PLTD	TWO 0.35	222N	2-1.35	101	II	3.6±0.2
				0.381X42.47		12129498	B1	B2	P3607336 425 TIN BRS 1/2 HD SN PLTD	3-2	13	3.8-2.45	103	II	4
						12124085	A1	A2	P3607336 425 TIN BRS 1/2 HD SN PLTD	0.8-0.5	19	3.12-2.03	101	I	3.2
12124106	A1	A2		0.381X42.47	PM001403 336 260 CART BRS 1/2 HD	12084586	B1	B2	P3607336 425 TIN BRS 1/2 HD SN PLTD	5-3	11	5.24-3.49	103	I	4.6
12066270	A1	A2		0.381X42.47	PM001403 336 260 CART BRS 1/2 HD	12066271	B1	B2	P3607336 425 TIN BRS 1/2 HD SN PLTD	0.5-0.35	21	-	101	II	2.4±0.2
12078175	B1	OBSOLETE		0.381X42.47	PM001403 336 260 CART BRS 1/2 HD	12052825	E1	OBSOLETE	P3607336 425 TIN BRS 1/2 HD SN PLTD	3	12	3.2-3.04	103	I	4.6
12020389	E1	E2		0.381X42.47	PM001403 336 260 CART BRS 1/2 HD	12034047	F1	D2	P3607336 425 TIN BRS 1/2 HD SN PLTD	0.8-0.5	19	3.12-2.03	101	I	3.2
				0.381X42.47		12020782	F1	F2	P3607336 425 TIN BRS 1/2 HD SN PLTD	TWO 0.35	222	2-1.35	101	II	3.6±0.2
				0.381X42.47		12020781	E1	OBSOLETE	F1403336 260 CART BRS 1/2 HD SN/CU PLTD	0.35	22	2-1.35	101	II	2.2±0.2
12078176	A1	OBSOLETE		0.381X42.47	PM001403 336 260 CART BRS 1/2 HD	12020117	C1	OBSOLETE	F1403336 260 CART BRS 1/2 HD SN/CU PLTD	5-3	11	5.24-3.49	102	I	4.6
12020388	B1	B2		0.381X42.47	PM001403 336 260 CART BRS 1/2 HD	12020116	D1	D2	P3607336 425 TIN BRS 1/2 HD SN PLTD	2-1	15	3.97-2.48	102	I	3.7
				0.381X42.47		12020115	G1	OBSOLETE	F1403336 260 CART BRS 1/2 HD SN/CU PLTD	0.8-0.5	19	3.12-2.03	101	I	3.2

PART DRAWING	
Uigraphics	THIRD ANGLE PROJECTION 
CODE NO 6900	QC METRIC
DWG DATE 14AP97	DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED
SCALE 10:1	DES
REFERENCE NO 001,701	DRH., CASTRILLON 14AP97 OKR., RAMOS S. 14AP9B APPR. DUGOS CUMMINGS 02MY97 VOL CM
MATERIAL SPEC	
SEE CHART	
TERM M M/P 280 SER	
PART NUMBER 1202 0114	SIZE AO
SHEET 1 OF 2	

THE DIMENSION NUMBER(S) SHOWN BELOW INDICATE DIMENSIONS THAT ARE PROCESS SENSITIVE FOR PART PRODUCTION		
(4)	(7)	(11-12)
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		
DIMENSIONAL RANGE		
FROM TO	0 12	> 12
TOLERANCE UNLESS OTHERWISE SPECIFIED		
	+0.1	+0.2
ANGULAR TOLERANCE ± 2°		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12020782](#)