

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P	CHG						
12MY05	R	01	-	-		ALL PARTS - RELEASED	266928	HAM	HAM	DMB
14JN05	R	02	-	-		09350754 REV E WAS 01, 12201057 REV B WAS 01 & WAS PART NO. IM12-4, 09357191 REV C WAS 01 & WAS PART NO. IM11-4	268676	DAD	DAD	DMB




PART NO.	SIZE	"A"	"B"	"C" REF.	"D"
IM06-4774	2 X 6	17.90[.705]	6.0[.24]	20.5[.81]	15.00[.591]
IM07-4774	2 X 7	20.90[.823]	6.0[.24]	23.5[.93]	18.00[.709]
IM08-4774	2 X 8	23.90[.941]	12.0[.47]	26.5[1.04]	21.00[.827]
IM09-4774	2 X 9	26.90[1.059]	12.0[.47]	29.5[1.16]	24.00[.945]
IM10-4774	2 X 10	29.90[1.177]	18.0[.71]	32.5[1.28]	27.00[1.063]
IM11-4774	2 X 11	32.90[1.295]	18.0[.71]	35.5[1.39]	30.00[1.181]
IM12-4774	2 X 12	35.90[1.413]	24.0[.94]	38.5[1.52]	33.00[1.299]

NOTES:


- HOUSING MATERIAL: PBT, 30% GLASS FILLED, COLOR - NATURAL
- CONTACT MATERIAL: BRASS, 1/2 HARD,
1.01±.03[.0398±.0010] DIA. OVER PLATING.
- CONTACT PLATING: .000050 MIN. THK. NI UNDERPLATE ALL OVER,
.000100-.000250 THK. Sn/Pb 90/10 ALL OVER.
- PIN RETENTION IN HOUSING: 5 LBS. MIN. PER PIN.
- RECTANGULAR PCB CUTOUT MUST BE SIZED FOR CHOSEN RECEPTACLE.
- HOUSING MATERIAL: P/N IM11-4774; PBT, 30% GLASS FILLED,
COLOR - BABY BLUE.

RECOMMENDED PCB LAYOUT

RETENTION LATCH
FOR SOLDER PROCESS (4)




ODD SIZE SHOWN. NOTE STANDOFF LOCATIONS



DIMENSIONS SHOWN IN INCHES ALTERNATE METRIC/INCH OR METRIC [INCH]	
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 5°	
METRIC	ENGLISH
1 PLACE ± 0.3	2 PLACE ± .01
2 PLACE ± 0.15	3 PLACE ± .008
3 PLACE ± 0.051	4 PLACE ± .0020

INVERSE HEADER, 3MM PITCH, 2 ROW
THROUGH HOLE



SPECIALTY
ELECTRONICS
LANDRUM, SC 29356 USA

SHEET NO.	DATE
1 OF 1	10-28-97
PART NO.	SEE TABLE
DRAWING NO.	CD4774
SIZE	C

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN.
- PART TO MEET THE REQUIREMENTS OF C4006 WHEN MATED
- (1.5)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

09357191	C	-	-	IM12-4	2 X 12	35.9 [1.413]	24 [.94]	38.5 [1.52]	33 [1.299]
12201057	B	-	-	IM11-4	2 X 11	32.9 [1.295]	18 [.71]	35.5 [1.391]	30 [1.181]
09350754	E	-	-	IM06-4	2 X 6	17.9 [1.070]	6 [.24]	20.5 [1.52]	15 [1.591]
PART NO	REV	N/P	STATUS	PART NO	SIZE	"A"	"B"	"C"	"D"

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM ³)	DISTR CODE		
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
13516887			
THIRD ANGLE PROJECTION	DO NOT SCALE	USE MATH DATA	

DELPHI			
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH			
DR	DATE		
APVD1	HOLLY A. MEEKER	12MY05	
APVD2	HOLLY A. MEEKER	12MY05	
APVD3	DAVID M. BERENDT	16MY05	
APVD4			
APVD5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001			
MATERIAL SEE DRAWING			
DRAWING NAME			
TAXI ASM CONN M HEADER			
DRAWING NUMBER			
09357187			
SIZE	SCALE	FRAME NO	SHEET NO
A2	N/A	1 OF 1	1 OF 1
STG	REV	N/P	
R	02	-	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[09350754](#)