






SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	43
	LAST NO. USED	25

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APPROVAL	
DATE	STATUS	REV	N/P	CHG					1	2
L	17DEC01	R	01	-		CLEARED REV COL: ALL PARTS - REDRAWN TO PD, ADDED QTY LVSID & MAT'L RECYCLING CODE NOTES, ADDED THREADED INSERT LABEL AND REVISED MATERIAL SPEC	218821	JORG	JOV	JH
	12AP05	R	02	-		ALL PARTS - 15498984 INSERT WAS 12065853 AND REVISED NUC	266723	JS	JS	MR
	18MY05	R	03	-		12160959 - MAT'L SPEC WAS M2191001 12193503 - MAT'L SPEC WAS M2191003	268238	MJM	MJM	MR



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. MATERIAL RECYCLING CODE >PBT PER SAE J1344. (2,3)x10.1) RAISED
CHARACTERS AS SHOWN ON ANY EXTERIOR SURFACE.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
3. MATING COMPONENTS OR EQUIVALENT:
CONNECTOR ASSEMBLY 12065850
4. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
SOLIDING SHROUD 12065847
SECONDARY LOCK COMB 12065848
CAVITIES A1,A2,A3,K1,K2 & K3 TO ACCEPT 480 SERIES TERMINAL
12052172
CAVITIES B1,B2,B3,B4,C1,C4,D1,D2,D3,D4,E1,E4,F1,F4,G1,G2,G3,
G4,H1,H4,J1,J2,J3 & J4 TO ACCEPT 280 SERIES TERMINAL 12040559
SEAL 12065849
5. (2,3)x10.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

12193503	02	AA		M4695003 PBT GRA	49.627
12160959	03	AA		M4695002 PBT BLK	49.627
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	VOLUME CM³

N/A PROCESS SENSITIVE DIMENSION										ALL DIMENSIONS ARE IN MILLIMETERS																																									
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED										REFERENCE																																									
<table><tr><th colspan="2">DIMENSIONAL RANGE (MM)</th><th colspan="2">CHART F1</th></tr><tr><td>FROM</td><td>TO</td><td>> 0</td><td>> 30</td></tr><tr><td></td><td></td><td>> 20</td><td>> 30</td></tr><tr><td></td><td></td><td>100</td><td>150</td></tr><tr><td></td><td></td><td>150</td><td>200</td></tr><tr><td></td><td></td><td>200</td><td>250</td></tr><tr><td></td><td></td><td>250</td><td>300</td></tr><tr><td></td><td></td><td>300</td><td>400</td></tr></table>										DIMENSIONAL RANGE (MM)		CHART F1		FROM	TO	> 0	> 30			> 20	> 30			100	150			150	200			200	250			250	300			300	400	THIRD ANGLE PROJECTION									
DIMENSIONAL RANGE (MM)		CHART F1																																																	
FROM	TO	> 0	> 30																																																
		> 20	> 30																																																
		100	150																																																
		150	200																																																
		200	250																																																
		250	300																																																
		300	400																																																
TOLERANCE UNLESS OTHERWISE SPECIFIED										DO NOT SCALE																																									
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2										USE MATH DATA																																									

DELPHI DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH							
DR						DATE	
APVD1 R.ORTIZ						02AUJ96	
APVD2 E.BAEZ						12AUJ96	
APVD3 C.WATKINS						23AUJ96	
APVD4							
APVD5							
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001							
MATERIAL							
SEE CHART							
DRAWING NAME							
TAXI CONN 30 M M/P 280 480							
DRAWING NUMBER							
15305440							
SIZE	SCALE	FRAME NO	SHEET NO	STS	REV	N/P	
A0	2:1	OF 1	OF 1	R	03		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12193503](#)