






MISSING SYMBOLS		DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APPROV	APPROV
		DATE	STG	REV	N/P	CHG						
NO MISSING SYMBOL NUMBER	20JAN04	R	01	-	-		ALL PARTS - REDRAWN TO PD	2450691	RCH	ESF	EST	
	10JAN04	R	02	-	-		REVISED TOLERANCES (6 PLCS)	255891	REH	ESF	EST	
	09MR06	R	03	-	-		08900542 - MAT'L SPEC WAS M3592002	2783751	JOA	F08	PPY	



1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. MATERIAL RECYCLING CODE PER ISO 14669, (.030)X(.003) RAISED
CHARACTERS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
3. (.030)X(.003) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.



DWG TYPE		PART DRAWING	
STYLE			
VOLUME (IMP)		DISTR CODE	
SEE CHART		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE ASME Y14.5M-1994 ADDENDUM 1 TOLERANCE ADDENDUM-2001. SEPARATE PATTERNS OF REFERENCE ARE ISSUED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN INCHES			
REFERENCE			
ON			
THIRD ANGLE PROJECTION	DO NOT SCALE		
	USE MATH DATA		

DELPHI DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH						
DP					DATE	
AP/02	R.	CHACON			20.JA.04	
AP/02	E.	SALAZAR			21.JA.04	
AP/03	E.	TRACEY			22.JA.04	
AP/04						
AP/05						
SUBSTANCES OF CONCERN AND REJECTED CONTENT PER DELPHI 10949001						
MATERIAL SEE CHART						
DRAWING NAME						
TAXI CONN F 56						
DRAWING NUMBER						
02984379						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	
A0	1:1	OF 1	OF 1	B	03	

08900542	04	-		M3592024 PA66 HS IM CRM	3.330
02984378	C2	-		M2043002 PP TD40 BLK	3.330
02977045	C2	-		M2043001 PP TD40 GRA	3.330
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	VOL CM³

9	PROCESS SENSITIVE DIMENSION				
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED					
DIMENSIONAL RANGE (IN)		CHART			
FROM	0	>.750	>1.250	>2.750	>4.0
TO	.750	1.250	2.750	4.000	
TOLERANCE UNLESS OTHERWISE SPECIFIED					
	±.005	±.010	±.012	±.016	±.020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[02977045](#) [08900542](#)