




SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	50	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	14		


DWG STATUS				ZONE		REVISION HISTORY		AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG							
25A004	R	D3	-	-			CLEARED REV COL. REDRAWN TO PD AND RESTRICTED USAGE.	255795	JDA	FRG	MGR
03AP06	R	D4	-	-			OBSOLETE AND ADDED NOTE	278753	6PS	FRG	RMD



2X THIS SURFACE OF SEAL MUST NOT BE OUTSIDE OF SHROUD.



- NOTES
1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 2. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: CAVITIES TO ACCEPT 12047680 TERMINAL OR EQUIVALENT.
 3. REFERENCE MATING COMPONENTS OR EQUIVALENT: CONNECTOR 12034401
 4. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
 5. BOLT TO BE RETAINED IN ASSEMBLY TO A MIN. 400 N.
 6. RECOMMENDED MATING TORQUE: 0.8 N-M TO 1.5 N-M.
 7. BOLT MUST ROTATE IN CONNECTOR AT A TORQUE OF LESS THAN 0.6 N-M AFTER RETAINER IS ASSEMBLED.
 8. SEALING CODE 3 - DESIGN WILL PASS SALT FOG AND IMMERSION TEST AFTER CONDITIONING AS SPECIFIED IN ESA-6444 (WEATHER-PACK), ESA-710 (METRI-PACK), ESA-650 (UNDERHOOD MICRO-PACK), C-4006 (WORLD CONNECTOR), ETC WHEN MATED TO MATING PART OR EQUIVALENT



(N/A) PROCESS SENSITIVE DIMENSION									
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED									
TOLERANCE UNLESS OTHERWISE SPECIFIED									
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
TO	20	30	70	100	150	200	250	300	400
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2
	ANGULAR TOLERANCE 22°								

DWS TYPE		PART DRAWING	
STYLE			
VOLUME 10/1		DISTR CODE	D
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE IN-SITU DIMENSIONING AND TOLERANCE ADDENDUM-2001. SEPARATE MATING OR FEATURES MAY BE DIMED SEPARATELY REBOLDED BY DATUM REFERENCE.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION			
DO NOT SCALE			
USE MATH DATA			

OBSOLETE
REPLACED BY
15492344

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
APVD1 R.W. GLEASON	06APB3
APVD2 GREG GAMBLE	08APB3
APVD3 J.M. CHUPAK	08APB3
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE DRAWING	
DRAWING NAME	
ASM CONN 30 F M/P 150 NAT SLD	
DRAWING NUMBER	
12034404	
SIZE A0	SCALE 5:1
FRAME NO 1	SHEET NO 1 OF 1
STG REV R	N/P D4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12034404](#)