






NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE >PBT< PER SAE J1344. (2.3)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- MATING COMPONENTS OR EQUIVALENT: CONNECTOR 12052447
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: TERMINAL 12089660 MAX INSULATION CRIMP MUST BE LESS THAN 2.3 HIGH AND 3.5 WIDE. SECONDARY LOCK 12052446 MAX CABLE O.D. 2.4 (REFER TO ESA-605 FOR CRIMP DIMENSIONS)
- (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

SYMBOL DEFINITION			MISSING NUMBERS	
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	24		
	LAST NO. USED	28		


DWG STATUS					REVISION HISTORY			AUTH	DR	CK	APVD
DATE	STG	REV	CHG	N/P	ZONE						
27MR02	R	D5	-	-		ADDED DELPHI LOGO, NOTES 2 AND 5 & REVISED MAT'L SPEC			222647	LEG	BEG 60

DELPHI Automotive Systems			
MATERIAL SPEC M4695002 PBT BLK			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI-A 10949001			
PART DRAWING		DISTR CODE	
CODE NUMBER 6901	DWG DATE 30NOB4	SCALE 5:1	D
OC SPEC	STYLE	VOLUME cm ³ 2.664	
PART GEOMETRY		UNLESS OTHERWISE SPECIFIED:	
 CHANGE RESTRICTED NO MANUAL CHANGES		THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M - 1994 AS AMENDED BY THE 6M GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
COPY OF MATH DATA DO NOT SCALE		REFERENCE	DATE
METRIC UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS		DR	
		APVD1 L.E. TURKSON	19DEB4
		APVD2 F. HESTON	07DEB4
		APVD3 B. SERBIN	18JA85
		APVD4	
THIRD ANGLE PROJECTION		DRAWING NAME	
		CONN 8F MIC/P 100	
SHEET NUMBER		DRAWING NUMBER	
OF		12052444	
		DWG STATUS	SIZE
		STG REV N/P	
		R D5 -	

DIMENSIONAL RANGE (MM)										CHART E1	
FROM	TO	0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	
		20	30	70	100	150	200	250	300	400	
TOLERANCE UNLESS OTHERWISE SPECIFIED											
		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	
ANGULAR TOLERANCE ± 2°											


SHARP CORNER TOLERANCE


(19) PROCESS SENSITIVE DIMENSION


DIMENSIONS ENCLOSED IN [] INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12052444](#)