






SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	18	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	11		

DATE		STG	REV	N/P	CHG	ZONE	REVISION HISTORY		AUTH	DR	APVD	APVD
22FE05	R	C3	-	-	-	-	CLEARED REV COLUMN, REDRAWN TO PD AND UPDATED MAT'L SPEC		264681	JPB	JAA	ET
09JUN05	R	C4	-	-	-	-	REVISED GRAPHICS		268957	MJM	MJM	BG
06JUL05	R	O4	-	-	-	-	MAT'L SPEC WAS M3592002		269717	RTV	JVM	EST
05DEC05	R	O4	AA	-	-	-	REVISED GRAPHICS: UPDATED DELPHI LOGO AND ADDED RECYCLING CODE, DIM #5 WAS 3X 1.5		275193	JPH	JAA	BDG



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1)CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
BOC EUROCOLUMN IGNITION SWITCH 26014526,
REFERENCE LAYOUT 12092222.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CAVITIES A, B & C TO ACCEPT 12066276 TERMINAL.
MAX INSULATION CRIMP MUST BE LESS THAN 4.85 HIGH AND 7.5 WIDE.
CAVITIES D, E & F TO ACCEPT 12020137 TERMINAL.
MAX INSULATION CRIMP MUST BE LESS THAN 3.4 HIGH AND 4.2 WIDE.
CAVITIES A, B & C TO ACCEPT 12085034 SECONDARY TERMINAL LOCK.
CAVITIES D, E & F TO ACCEPT 12085033 SECONDARY TERMINAL LOCK.
CONNECTOR POSITION ASSURANCE LOCK 12052834
- (1.5)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.



VIEW SCALE DOES NOT REFLECT ACTUAL PART SIZE

		11		PROCESS SENSITIVE DIMENSION	
		DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART F			
FROM	> 0	> 20	> 30	> 70	> 100
TO	> 20	> 30	> 70	> 100	> 150
TOLERANCE UNLESS OTHERWISE SPECIFIED		> 150	> 200	> 250	> 300
	±0.15	±0.2	±0.3	±0.4	±0.5
				±0.6	±0.8
		ANGULAR TOLERANCE ±2°			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12110075](#)