




SYMBOL DEFINITION		MISSING NUMBERS		DWG STATUS		ZONE		REVISION HISTORY		AUTH		DR		AP/D	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.		TOTAL NO. OF SYMBOLS ON DRAWING		DATE		STG		REV		N/P		CHG		Cleared revision column: all active parts - added notes 2 and 5, revised tol (2 PLCS) and mat'l spec	
		26		10JUN02		R		03		-		-		214553	
		37		160003		R		04		-		-		247506	
				130005		R		05		-		-		273384	
				120006		R		06		-		-		285012	
				12MR07		R		07		-		-		400766	




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN





TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN







TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101



OPTIONAL CONSTRUCTION
ALL TYPES

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469, (2.3)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 12048074
TERMINAL POSITION ASSURANCE LOCK 12066304
- (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

15324168	A1	-	OBSOLETE	103	M3592001 PA66 HS 1M BLK	15324167	OBSOLETE	15324170	5	A, H & D	5.689
12124017	C6	-		105	M3592010 PA66 HS 1M BRN	12124647	-	ABS SENSOR	4	A, D, E & H	5.757
12092493	04	AB	OBSOLETE	104	M3592024 PA66 HS 1M CRM	12092494	OBSOLETE	12047931	6	C & F	5.662
12052499	F6	-		103	M3592025 PA66 HS 1M GRA MD	12052600	-	12052480	5	A, H & D	5.689
12047934	L6	-		102	M3592012 PA66 HS 1M GRA LT	12047938	-	12047933	7	D	5.683
12047932	L6	-		101	M3592001 PA66 HS 1M BLK	12047937	-	12047931	8	NONE	5.687
PART NO	REV	N/P	STATUS	TYPE	MATERIAL SPECIFICATION AND COLOR	ASSEMBLY NUMBER	STATUS	MATING CONNECTOR	CAVITIES	CAVITIES BLOCKED	VOL CM ³

(10) PROCESS SENSITIVE DIMENSION DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED										CHART E										THIRD ANGLE PROJECTION										DO NOT SCALE																																																																																																			
DIMENSIONAL RANGE (MM)																																																																																																																																	
FROM										> 0										> 20										> 30										> 70										> 100										> 150										> 200										> 300										> 400																																							
TO										20										30										70										100										150										200										300										400																																																	
										TOLERANCE UNLESS OTHERWISE SPECIFIED																																																																																																																							
										±0.15										±0.2										±0.3										±0.4										±0.5										±0.6										±0.8										±1										±1.2																																							
										±0.15										±0.2										±0.3										±0.4										±0.5										±0.6										±0.8										±1										±1.2																																							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12047934](#) [12052600](#)