





SYMBOL DEFINITION			MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	12		
	LAST NO. USED	31		

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
19SE03	R	E1	-	-		CLEARED REV COL, MAT'L SPEC WAS R0071676, ADDED NOTES (2 PLCS) AND REVISED TOL	246187	EGR	EGR	EM
24SE03	R	E2	-	-		ADDED DIM & REVISED DIM	246377	EGR	EGR	EM



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- MATING COMPONENTS OR EQUIVALENT: MOUNTING BASE 12077534
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: COVER 12077538
CAVITIES A1 - A8 TO ACCEPT 12065916 TERMINAL ASSEMBLY OR EQUIVALENT.
CAVITIES B1 - B8 TO ACCEPT 12065930 TERMINAL ASSEMBLY OR EQUIVALENT.
MAX INSULATION CRIMP MUST BE LESS THAN 5.3 HIGH AND 10.05 WIDE.
SECONDARY TERMINAL LOCK 12077532
MAX CABLE O.D. MUST BE LESS THAN 5.8
- (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE. PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

DWG TYPE				PART DRAWING	
STYLE					
VOLUME (CM)				DISTR CODE	
ROUTING				6900	

UNLESS OTHERWISE SPECIFIED
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
AS AMENDED BY THE 2018 GLOBAL DIMENSIONING AND TOLERANCING STANDARD (GD&T). SEPARATE PATTENING OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.

ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE

(31) PROCESS SENSITIVE DIMENSION

DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

THIRD ANGLE PROJECTION

DO NOT SCALE USE MATH DATA

SHARP CORNER TOLERANCE

DIMENSIONAL RANGE (MM)

FROM > 0 TO > 20 > 20 TO > 70 > 70 TO > 100 > 100 TO > 150 > 150 TO > 200 > 200 TO > 250 > 250 TO > 300 > 300 TO > 400

TOLERANCE UNLESS OTHERWISE SPECIFIED

ANGULAR TOLERANCE ±2°

DELPHI				DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR				DATE	
APVD1 JORGE IBARRA				050C98	
APVD2 FCO. KOPCA				150C98	
APVD3 G. MOLINA				240C98	
APVD4					
APVD5					
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001					
MATERIAL M4692002 - PA66 GF33 HS BLK					
DRAWING NAME				CENT FUS BLK MAXI BLK PRINTED	
DRAWING NUMBER				12110415	
SIZE A0				SCALE 2:1	
FRAME NO 1				SHEET NO 1 OF 1	
STG REV N/P				R E2 -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12110415](#)