


PART NO
1212 9426


[illegible]

- SEE DETAIL "Z"

SECTION A - A


NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. HARDNESS TO BE ROCKWELL "C" 25-32
(TO BE CHECKED ON THREADED END.)
3. ZINC PLATE, CHROMATE TREAT AND COLOR DYE
PER GM-4342-M CODE 20Z24 (BLUE)
4. MATING CONNECTOR BODY 12092201 OR EQUIVALENT.
PART TO MATE 12092191 #10-24 THREAD INSERT OR EQUIVALENT.
5. BOLT MUST BE CAPABLE OF WITHSTANDING A MINIMUM
OF 8.5 N-M (75 IN-LBS) OF TORQUE WITHOUT FAILURE
6. MAXIMUM WEIGHT OF CARTON & CONTENTS SHALL NOT
EXCEED 29 LBS. RECOMMEND 8X6X6 INCH CARTON WITH
1700 BOLTS.
7. BOLT TO ACCEPT 12034236 RETAINER OR EQUIVALENT
SEE 12092202 ASM.DWG.
8. BOLT HEAD DESIGN FOR 7MM HEX SOCKET
9. * MUST BE MAINTAINED THROUGHOUT LENGTH OF
HEX HEAD
10. PART MUST BE FREE OF RUST AND OILY GRIT



OBSOLETE

PART NO
1212 9426

PART DRAWING		THIRD ANGLE PROJECTION	
Unigraphics			
CODE NO 6901	QC	ENGLISH DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED	
DWG DATE 090C91		DES	
SCALE 5:1		DR W.L. STEIN 090C91	
REFERENCE NO 001,701		CK HENRY HOBE 220C91	
12110238		APPR W.L. STEIN 220C91	
		VOL CM ³	
MATERIAL SPEC SAE01038 STL			
NAME BOLT HEX HD FLG H			
PART NUMBER 1212 9426			SIZE A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12129426](#)