








SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	15
	LAST NO. USED	11

MISSING SYMBOLS
NO MISSING SYMBOL NUMBER

DWG STATUS					ZONE	REVISION HISTORY		AUTH	DR	1	
DATE	STG	REV	N/P	CHG						APVD1	APVD2
04DE06	R	01	-	-		WAS PE158091. ADDED NOTE 6 AND RELEASED		287495	MB	MB	JRM
15DE06	R	02	-	-		UPDATED PDM ATTRIBUTES		287810	JS	JS	JRM
17JA07	R	02	AA	-		UPDATED PDM ATTRIBUTES		400090	JS	JS	JRM
09FE07	R	03	-	-		UPDATED WITH LATEST CAVITY STANDARD		400486	LLJ	LLJ	JRM
27FE07	R	04	-	-		UPDATED WITH LATEST CAVITY STANDARD		400649	JMR	JMR	JRM
13MR07	R	04	AA	-	-	REVISED TOLERANCE ON DIM 9 & ADDED OPTIONAL CONSTRUCTION TO MATERIAL RECYCLING AND DELPHI CORPORATE BRAND LOGO NOTES.		400786	LLJ	LLJ	JRM
27AP07	R	05	-	-		UPDATED WITH LATEST CAVITY STANDARD		401243	LLJ	LLJ	JRM



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR YAZAKI PART NUMBER 7282-1020
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 13592500
- MATERIAL RECYCLING CODE PER ISO 11469. (1)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION IS NO MATERIAL RECYCLING CODE.
- (1)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION IS NO DELPHI CORPORATE BRAND LOGO.
- TERMINAL POSITION REQUIRES THE USE OF A DELPHI PACKARD NORTH AMERICA ELECTRICAL TEST HOLDER OR A DELPHI PACKARD NORTH AMERICA APPROVED EQUIVALENT. FAILURE TO DO SO CAN RESULT IN UNSEATED TERMINALS.

1 PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART ET
FROM TO	
> 0 TO 20	> 20 TO 30
> 30 TO 70	> 70 TO 100
> 100 TO 150	> 150 TO 200
> 200 TO 250	> 250 TO 300
> 300 TO 400	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2	
ANGULAR TOLERANCE ±2°	

DWG TYPE	
PART DRAWING	
STYLE	
VOLUME (CM ³)	DISTR CODE
1.227	D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2001 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	NX

DELPHI						
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH						
DR			DATE			
APVD1	M. BASHKIN		04DE06			
APVD2	M. BASHKIN		04DE06			
APVD3	JOHN MORELLO		04DE06			
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001						
MATERIAL M4695001 PBT NAT						
DRAWING NAME						
CONN 2 F 090 11 FBT NAT						
DRAWING NUMBER						
13597206						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	05	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13597206](#)