







SYMBOL DEFINITION		MISSING SYMBOLS		DATE		STG		REV		N/P		CHG		ZONE		REVISION HISTORY		AUTH		DR		APVD	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.		TOTAL NO OF INSPECTIONS REQUIRED		02A005		R		01		-		-		-		13536533-41 WERE PE142285-93 & RELEASED		270573		JS		JS	
		LAST NO. USED		16A005		R		02		-		-		-		ALL PARTS - CLIP P/N WAS 15411124, REVISED NOTE #4		271188		END		END	
				04N005		R		03		-		-		-		ALL PARTS - REVISED OHMS RESISTANCE VALUES ON CONNECTORS AND REVISED CHART		273978		MM		MM	
				06JN06		R		04		-		-		-		ALL PARTS - REVISED CUSTOMER PART NUMBER AND SPEC IN NOTE 4		281171		MM		MM	



RESISTANCE VALUE (2.3)X(0.1)
SEE CHART FOR VALUE



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- ASSEMBLY: BE SURE TO SEAT CLIP SECURELY IN THE CONNECTOR BODY CLIP SLOT.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 15326801
- PARTS MUST MEET BORGWARNER SPEC 44-00-430-039-C AND 44-00-447-00B.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 15326426
(FEMALE TERMINAL MUST HAVE GOLD PLATED TERMINAL CONTACT AREA)

44-00-694-009	13536541	03	AA	-	13534895	12700	15326712
44-00-694-008	13536540	03	AA	-	13534894	7320	15326712
44-00-694-007	13536539	03	AA	-	13534893	3160	15326712
44-00-694-006	13536538	03	AA	-	13534892	1820	15326712
44-00-694-005	13536537	03	AA	-	13534891	1150	15326712
44-00-694-004	13536536	03	AA	-	13534890	715	15326712
44-00-694-003	13536535	03	AA	-	13534889	453	15326712
44-00-694-002	13536534	03	AA	-	13534888	255	15326712
44-00-694-001	13536533	03	AA	-	13534887	115	15326712
BORGWARNER PART NO	PART NO	REV	N/P	STATUS	CONN ASM	RESISTANCE (OHMS ±1%)	CLIP

N/A PROCESS SENSITIVE DIMENSION										REFERENCE	
DIMENSIONS ENCLOSED IN $\square$ INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED											
DIMENSIONAL RANGE (MM)										QUANT. LT.	
FROM		> 20		> 30		> 70		> 100		> 150	
> 20		> 30		> 70		> 100		> 150		> 200	
> 30		> 70		> 100		> 150		> 200		> 250	
> 70		> 100		> 150		> 200		> 250		> 300	
> 100		> 150		> 200		> 250		> 300		> 400	
TOLERANCE UNLESS OTHERWISE SPECIFIED											
± 0.15		± 0.2		± 0.3		± 0.4		± 0.5		± 0.6	
> 0.15		> 0.2		> 0.3		> 0.4		> 0.5		> 0.6	
ANGULAR TOLERANCE $^{\circ}$											
± 1		± 2		± 3		± 4		± 5		± 6	
> 1		> 2		> 3		> 4		> 5		> 6	

THIRD ANGLE PROJECTION	DO NOT SCALE		USE MATH DATA	
---------------------------	-----------------	---	------------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13536536](#) [13536535](#) [13536533](#) [13536534](#) [13536537](#) [13536538](#)