






- ## NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. SEALING CODE 0 - UNSEALED
3. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CAVITIES A1 TO A6, C1 TO C6, H1 TO H6 & K1 TO K6 TO ACCEPT 12191811 TERMINAL OR EQUIVALENT.
MAX INSULATION CRIMP MUST BE LESS
THAN 5.32 HIGH AND 2.85 WIDE.
CAVITIES G1, G2, B3, D1, E1, E2, F2, F3, G1, G2, J1, J2 & J3 TO ACCEPT 15304711 TERMINAL OR EQUIVALENT.
MAX INSULATION CRIMP MUST BE LESS
THAN 5.32 HIGH AND 5.15 WIDE.
CAVITIES E3 & F1 TO ACCEPT 12065915 TERMINAL OR EQUIVALENT.
MAX INSULATION CRIMP MUST BE LESS
THAN 6.3 HIGH AND 9.7 WIDE.
SECONDARY TERMINAL LOCK 15477824 OR EQUIVALENT.
INSERT 15410323 OR EQUIVALENT
WIRE DRESS COVER 13552252 OR EQUIVALENT.
CAM LEVER 13552253 OR EQUIVALENT.

4. REFERENCE DIMENSIONS ARE TO MATING BLADE CENTERLINES.
5. MATERIAL RECYCLING CODE PER ISO 11469. (2,3)X(0,1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
6. (2,3)X(0,1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.

13552256	01	AA			M4629012 PBT GF20 GRA LT	103	27.218
13552255	01	AA			M4629003 PBT GF20 GRA	102	27.218
13552254	01	AA			M4629002 PBT GF20 BLK	101	24.218
PART NO	REV	N/P	STATUS		MATERIAL SPECIFICATION AND COLOR	TYPE	VOLUME

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	53
	LAST NO. USED	41

MISSING SYMBOLS	DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APD1	APD2
	DATE	STG	REV	N/P	CHD						
NO MISSING SYMBOL NUMBER	02N004	R	01	-	-		ALL PARTS - RELEASED	260258	RCR	RCR	SD
	05N06	R	02	-	-		ALL PARTS - REVISED NOTE 5	281317	EAT	EAF	RVP

	31	PROCESS SENSITIVE DIMENSIONS
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		
DIMENSIONAL RANGE (MM)		CHART
FROM	TO	TOLERANCE
> 0	> 20	> 70
> 20	> 30	> 100
> 30	> 70	> 150
> 70	> 100	> 200
> 100	> 150	> 250
> 150	> 200	> 300
> 200	> 250	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED		
± 0.15	± 0.2	± 0.3
± 0.4	± 0.5	± 0.6
± 0.8	± 1	± 1.5

PLOT TYPE		PART DRAWING	
STYLE			
VOLUME (QTY)		DISTR CODE	
SEE CHART		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 IT IS MARKED BY THE 3M IN DIMENSIONAL DRAWING AND TOLERANCE ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MUST BE ISSUED SEPARATELY REGARDLESS OF DATA REPRESENTATION.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
1	THIRD ANGLE PROJECTION	DO NOT SCALE	 UNIGRAPHICS
2		USE: MATH DATA	

							
DELPHI PACK/AND ELECTRIC SYSTEMS WARREN, OH							
OR DATE				DATE			
API#01 R. CHACON				02N004			
API#02 R. CHACON				02N004			
API#03 S. DOMHOFF				02N004			
API#04				02N004			
API#05				02N004			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001							
MATERIALS SEE CHART							
DRAWING NUMBER TAXI CONN 4 W 0T 150 280 M/P 800							
DRAWING NUMBER 13552262							
SIZE	SCALE	FRAME NO	SHEET NO	STD	REV	N/P	
A0	2:1	1	OF 1	1	02		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13552254](#)