



Technical drawing of a mechanical part with dimensions:

- Overall width: 12.20
- Overall height: 3.30 ± 0.20
- Top left width: $2.20 \begin{smallmatrix} +0.30 \\ 0 \end{smallmatrix}$
- Top left height: $2.40 \begin{smallmatrix} +0 \\ -0.20 \end{smallmatrix}$
- Top middle width: 3.45 ± 0.2
- Top middle height: 7.30 ± 0.10
- Top right width: 9.90 ± 0.20
- Top right height: 0.80 ± 0.15
- Bottom left width: 2.95 ± 0.15
- Bottom left height: 1.40 ± 0.25
- Bottom middle width: 6.90 ± 0.20
- Bottom middle height: 0.85
- Bottom right width: 1.50 ± 0.1
- Bottom right height: 0.80



The front view shows a square flange with a central circular hole. A cross-shaped slot is cut into the center of the flange, passing through the hole. The flange has a thick, rounded outer edge.



Technical drawing of a mechanical part with dimensions and tolerances:

- Top horizontal dimension: $2.20 \pm \begin{matrix} +0.20 \\ -0.10 \end{matrix}$
- Second horizontal dimension from the left: 2.40 ± 0.50
- Third horizontal dimension from the left: $4.00 \pm \begin{matrix} +0.10 \\ -0.05 \end{matrix}$
- Bottom horizontal dimension: 0.50 ± 0.10
- Bottom horizontal dimension (total length): $3.40 \pm \begin{matrix} +0.10 \\ -0.05 \end{matrix}$

REFERENCES PARTNAME	211 CC 3 S 1160	211 CC 3 S 1161	211 CC 3 S 2160	211 CC 3 S 2161
PROTECTION PLATED	1 à 3 μ de Sn	1 à 3 μ de Sn	1 à 3 μ de Sn	1 à 3 μ de Sn
GAMME RANGE	1	1 (JUF)	2	2 (JUF)
SECTION / mm2 SECTION	0.35 / 0.75		1.00 / 2.50	
B	2.90		3.30	
C	2.20		3.60	
D $\pm$ 0.10	0.90		0.90	
F	4.00	4.20	4.70	4.90
G	3.30	4.10	4.90	5.30
H $\pm$ 0.10	1.40		1.40	1.70
K $\pm$ 0.10	0.60		0.60	
L $\pm$ 0.10	0.10		0.10	
QUANTITE PAR BOBINE QUANTITY PER REEL	3 500		2 800	
POIDS WEIGHT	14.5 Kg		11 Kg	

PSA

EUR P10 16 F27

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[211CC3S2161-L](#) [211CC3S2160-L](#)