






12
11
10
9
8
7
6
5
4
3
2
1
H
G
F
E
D
C
B
A

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	9
	LAST NO. USED	6

MISSING SYMBOLS	DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	CK	APVD
	DATE	STG	REV	CHG	N/P						
NO MISSING SYMBOL NUMBER	13SE01	R	001	-	-		WAS PE085736 AND RELEASED	212514	TSH	TSH	MJ



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- THIS PART USED IN ASSEMBLY TBD.
- MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 15404971
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 15401440
MAX INSULATION CRIMP MUST BE LESS
THAN 2 DIAMETER.
TERMINAL POSITION ASSURANCE LOCK 15404970
SEE DETAIL DRAWING FOR COMPATIBLE O.D. RANGE

		DIMENSIONAL RANGE (MM)										CHART E
		FROM TO	0 20	> 20 30	> 30 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300	> 300 400	
TOLERANCE UNLESS OTHERWISE SPECIFIED												
SHARP CORNER TOLERANCE												
± 0.15 ± 0.2 ± 0.3 ± 0.4 ± 0.5 ± 0.6 ± 0.8 ± 1 ± 1.2												
ANGULAR TOLERANCE $\pm 2^\circ$												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15404969](#)