






SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	12	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	11		


CWS STATUS				REVISION HISTORY				AUTH	DR	APVD	APVD
DATE	STG	REV	W/R	CHG	ZONE						
04AU04	R	01	-	-		RELEASED		257692	8PS	FRG	5AN
15AP05	R	01	AA	-		ADDED NOTE #3 AND 64 +0.3/-0.75 WAS		266999	CCV	FRG	TP
05MY06	R	01	AB	-		ADDED LABEL		280027	JTZ	FKV	TP
25JA13	R	01	AC	-		UPDATED MATERIAL SPEC		421223	DCH	JVM	RLG




SEE DETAIL A



2X 11
2X NO BURRS PERMISSIBLE TYP



DETAIL A
SCALE 5:1



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 12146432

- PLATING TO WITHSTAND 120 HOURS MIN TO RED RUST IN NEUTRAL SALT FOG, EXCEPT FOR SHARP EDGES.

- MATERIAL:
PREFERRED: ASTM A653CS TYPE B G90 COATED WITH TRIVALENT CHROMIUM
ALTERNATE: M5349 ASTM A653 CS TYPE B WITH CLEAR COAT

A. LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT DELPHI SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	PART DRAWING
STYLE	
VOLUME (OMP)	DISTR CODE
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE 2003 DIMENSIONING AND TOLERANCING ADDENDUM-2003. SEPARATE PATTERNING OF FEATURES MAY BE SHOWN SEPARATELY, RESOLVING OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	
DO NOT SCALE USE MATH DATA	

PROCESS SENSITIVE DIMENSION			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)	CHART	G	
FROM 0	> 12		
TO 12			
TOLERANCE UNLESS OTHERWISE SPECIFIED			
+0.15			
+0.3			
ANGULAR TOLERANCE 12°			

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE	
WARREN, OH	
COPYRIGHT 2004 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DATE	
DR	
APV01	PATRICIA SANCHEZ
APV02	FCO. RESENDIZ
APV03	SAMUEL NORLING
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (0944990)	
MATERIALS SEE NOTES	
DRAWING NAME	
COV CONN M/P	
DRAWING NUMBER	
15495857	
SIZE	SCALE
A0	2:1
FRME NO	1 OF 1
SHEET NO	1 OF 1
STG	REV
01	AC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15495857](#)