


Technical drawing of a mechanical part with a cross-section. The part has a central rectangular hole and two side holes. Dimensions are given in millimeters. The central hole has a diameter of 8x1.80 ± 0.05. The side holes have a diameter of 0.20 M. The part is shown in a cross-section view with a hatched area indicating the material. The drawing includes a title block with the text '0.20 M A B C' and a dimension line indicating the distance between the holes.

N° D'EMPREINTE DU PORTE-CLIPS
FEMALE HOUSING CAVITY NUMBER




The drawing shows a shaft-hub assembly with a cross-section. The shaft has a diameter of 40 ± 0.05 mm. The hub has a bore diameter of 40 ± 0.05 mm. The keyway in the hub has a width of 10 ± 0.05 mm. The detail view shows the keyway with a width of 10 ± 0.05 mm and a depth of 4 ± 0.05 mm. The detail view also shows the keyway with a width of 10 ± 0.05 mm and a depth of 4 ± 0.05 mm.

N° D'EMPREINTE DU LEVIER
LEVER CAVITY NUMBER



INDICE DU PORTE-CLIPS ASSEMBLE
REVISION LEVEL OF FEMALE CONNECTOR

[illegible]


LOGO DELPHI OU MVL-
DELPHI OR MVL LOGO

-INDICATION SORTIE FAISEAU (DROIT)
WIRING OUT INDICATION (RIGHT)


INDICATION SORTIE FAISCEAU (GAUCHE)
WIRING OUT INDICATION (LEFT)



LE LEVIER CACHE LA MAUVAISE
INDICATION DE SORTIE DE FAISCEAU
LEVER HIDE BAD WIRING OUT INDICATION




MODULE MODULE	PRODUITS ASSOCIES ASSOCIATED PARTS						
	CAPOT COVER		BOUCHON D'ALVEOLÉS CAPVITY PLUG				
			CAVITE 0.635 0.635 CAVITY		CAVITE 1.5 1.5 CAVITY		
	MVL P/N	DELPHI P/N	MVL P/N	DELPHI P/N	MVL P/N	DELPHI P/N	
32 VOIES 32 WAY	PP10001522	13851307	PP10001485	13768626	PP10001486	13826722	



CODAGE : EN ACCORD AVEC LA SPECIFICATION NF R 13-462
CODING : IN ACCORDANCE WITH NF R 13-462 SPECIFICATION

PRINCIPALES PROPRIETES MECANQUES MAIN MECHANICAL PROPERTIES	CT 0635	CT 15
FORCE D'INSERTION D'UN CONTACT TERMINAL INSERTION FORCE	10N MAXI	12N MAXI
EFFORT DE POLARISATION D'UN CONTACT A 90° ET 180° TERMINAL POLARISATION FORCE AT 90° AND 180°	24 MINI	30 MINI
EFFORT DE RETENTION AVEC DV RETENTION FORCE WITH SECONDARY LOCK	80N MINI	100N MINI
EFFORT SUR LE LEVIER D'ACCOUPLEMENT PC/PL MATING FORCE ON THE SLIDER DEVICE		65N MAXI
EFFORT SUR LE LEVIER DE DESACCOUPLEMENT PC/PL UNMATING FORCE ON THE SLIDER DEVICE		65N MAXI
EFFICACITE DE VERROUILLAGE FULL ENGAGED EFFICIENCY		200N MINI
CLASSE DE TEMPERATURE OPERATING TEMPERATURE		-40°C / +125°C
CLASSE DE VIBRATIONS VIBRATION CLASS		15 g
CLASSE D'ETANCHEITE SEALING CLASS		±0.5 Bar 1PX9K

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[PPI0001489](#)