




12		11		10		9		8		7		6		5		4		3		2		1																																					
SYMBOL DEFINITION														MISSING SYMBOLS		DWG STATUS				ZONE		REVISION HISTORY		AUTH		DR		APVD1		APVD2																													
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.														TOTAL NO OF INSPECTIONS REQUIRED		8		NO MISSING SYMBOL NUMBER		DATE		STG		REV		N/P		CHG		Cleared REV COL AND ADDED DEED LOGO & NOTE 3		287351		JBD		EVV		RAT																					
														LAST NO. USED		8																																											
																																																											
NOTES 1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA. 2. PARTS TESTED TO ES-T-486 WILL HAVE A MINIMUM AVERAGE DIELECTRIC BREAKDOWN VALUE OF 20 KV(RMS) WITH NO TEST VALUE LESS THAN 15 KV. 3. D.E.E.D. AND CAVITY NUMBER ARE (.091) X (.004) RAISED AND ARE LOCATED ON ANY EXTERIOR SURFACE VISIBLE AT FINAL ASSEMBLY. 6 PROCESS SENSITIVE DIMENSION DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED <table><tr><td colspan="2">DIMENSIONAL RANGE (IN)</td><td colspan="2">CHART</td><td colspan="2">H</td></tr><tr><td>FROM</td><td>0</td><td>>.750</td><td>>1.250</td><td>>2.750</td><td>>4.000</td></tr><tr><td>TO</td><td>.750</td><td>1.250</td><td>2.750</td><td>4.000</td><td></td></tr><tr><td colspan="6">TOLERANCE UNLESS OTHERWISE SPECIFIED</td></tr><tr><td colspan="6">±.005 ±.010 ±.012 ±.016 ±.020</td></tr><tr><td colspan="6">ANGULAR TOLERANCE ±2°</td></tr></table> DWG TYPE PART DRAWING STYLE VOLUME (CM³) 6.268 DISTR CODE D UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE SHOWN SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN INCHES REFERENCE THIRD ANGLE PROJECTION DO NOT SCALE USE MATH DATA   DELPHI DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH DR DATE APVD1 JOHN M. SOVA 25MY78 APVD2 D.E. LHEIG 31MY78 APVD3 S.C. DULAC 01JN78 APVD4 APVD5 SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001 MATERIAL M4992002 SILICONE BLK DRAWING NAME SLEV IGN BOOT BLK DRAWING NUMBER 08905588 SIZE A1 SCALE 2:1 FRAME NO 1 OF 1 SHEET NO 1 OF 1 STG R REV 07 N/P AD																								DIMENSIONAL RANGE (IN)		CHART		H		FROM	0	>.750	>1.250	>2.750	>4.000	TO	.750	1.250	2.750	4.000		TOLERANCE UNLESS OTHERWISE SPECIFIED						±.005 ±.010 ±.012 ±.016 ±.020						ANGULAR TOLERANCE ±2°					
DIMENSIONAL RANGE (IN)		CHART		H																																																							
FROM	0	>.750	>1.250	>2.750	>4.000																																																						
TO	.750	1.250	2.750	4.000																																																							
TOLERANCE UNLESS OTHERWISE SPECIFIED																																																											
±.005 ±.010 ±.012 ±.016 ±.020																																																											
ANGULAR TOLERANCE ±2°																																																											

12

11

10

9

8

7

6

5

4

3

2

1

12

11

10

9

8

7

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[08905588](#)