





SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	10
	LAST NO. USED	10

DWG STATUS					REVISION HISTORY				AUTH	DR	APVD
DATE	STG	REV	N/P	CHG	ZONE						
31MY01	R	001	-	-		ALL PARTS - WERE ON SHEET 2 TYPE 202	209330	FMD	FRG	ET	
20AU03	R	02	-	-		12103576 & 12089791 - REVISED PROCESS NOTE 3	244878	BYP	EAR	FR	M
26SEP03	R	03	-	-		15479729,31 - RELEASED AND ADDED NOTE 6	246528	LFS	RVP	OMC	
14JUN04	R	04	-	-		12047634, 12124478 - OBSOLETE AND ADDED NOTE 6	253207	ESH	JVM	SAN	
29JUL04	R	05	-	-		ADDED PARTS 15477650, 15477660, 15477667, 15477668 AND 15495701 - RELEASED	257338	RH	RH	SAN	
02DEC04	R	06	-	-		ALL ACTIVE PARTS - 2.85 +0.45/-0.15 WAS 2.85 +0.17/-0.15	261566	CTR	JAA	TP	
25OCT05	R	07	-	-		12089791, 12103576, 12129331, 12146502, 15305121, 15317395, 15479729 AND 15479731 - OBSOLETE	273251	MDH	JAA	P60	
28OCT05	R	08	-	-		12040637 - OBSOLETE	273621	MDH	JAA	P60	
06JUN06	R	09	-	-		REMOVED HEXAVALENT CHROME COATING NOTE; ALL ACTIVE PARTS - UPDATED PD INFO AND ADDED DIM #2	281427	JTZ	JAA	TP	




NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- PROCESS OPERATIONS TO BE PERFORMED IN SEQUENCE SHOWN IN CHART
- MATES TO 12033957 CLIP OR EQUIVALENT.
- THE PROCESS NOTES SHOWN ABOVE ALSO APPEAR ON THE CLIP ASSEMBLY -TAXI DWG 12034064.
- MISMATCH NOTCHES (OPTIONAL) 0.04 R MAX 0.04 DEEP MAX ALLOWED ON EDGES SHOWN

PROCESS NOTES

- ZINC PLATE AND GOLD CHROMATE PER GM-4342 CODE 10D24.
- PHOSPATE/ORGANIC/OIL TYPE COATING PER GM-6173-M BLACK.
- ZINC-ALUMINUM/INORGANIC TYPE COATING PER GM-6173-M BLACK
- PLATE TO "0.0003" MIN ZINC WITH BLACK CHROMATE, THEN 2 COATS LOW TEMP CURE BLACK ORGANIC, TOPCOAT, FINISH MUST WITHSTAND 400 HRS MIN TO RED RUST IN NEUTRAL SALT FOG, EXCEPT FOR SHARP EDGES.
- NIZN-COTE CHROMATE PLATE PER GM 0.000150 IN MIN THICKNESS, THIS PLATING IS USED FOR CONDUCTIVE APPLICATIONS.
- PLATING REQUIREMENTS TO WITHSTAND 168 HOURS MINIMUM TO RED RUST IN NEUTRAL SALT FOG, EXCEPT FOR SHARP EDGES.



15495701	01	AB		0.9	M4868	6	-	60	31.75	6.5	M6
15477668	01	AB		0.9	M4868	-	-	60	15.75	8.8	M8
15477667	01	AB		0.9	M4868	-	-	60	15.75	6.5	M6
15477660	01	AB		0.9	M4868	-	-	36.2	15.9	10.6	M10
15477650	01	AB		0.9	M4868	6	-	60	15.75	10.6	M10
15479731	01	AB	OBSOLETE	0.9	SAE 100B STL	3,6	-	60	31.75	6,5	M6
15479729	01	AB	OBSOLETE	0.9	SAE 100B STL	3,6	-	60	15.75	10,6	M10
15317395	A6	-	OBSOLETE	0.9	SAE 100B STL	4	-	60	15.75	8.8	M8
15305121	A7	-	OBSOLETE	0.9	SAE 100B STL	4	-	60	15.75	6.5	M6
12146502	A6	-	OBSOLETE	0.9	SAE 100B STL	5	-	60	15.75	6.5	M6
12129331	B4	-	OBSOLETE	0.9	SAE 100B STL	2	-	36.2	15.9	10.6	M10
12124478	A4	-	OBSOLETE	0.9	SAE 100B STL	1	-	60	8.5	5.4	M5
12103576	O3	AB	OBSOLETE	0.9	SAE 100B STL	3	-	60	31.75	6.5	M6
12089791	O2	AB	OBSOLETE	0.9	SAE 100B STL	3	-	60	15.75	10.6	M10
12047634	A6	-	OBSOLETE	0.9	SAE 100B STL	1	-	60	15.75	6.5	M6
12040637	C4	-	OBSOLETE	0.9	SAE 100B STL	1	-	60	15.75	10.6	M10
PART NO	REV	N/P	STATUS	SIZE	MATERIAL	PROCESS NOTES	APPLICABLE STOCK THK	A ±0.6	C ±0.3	ø K ±0.1	HOLE SIZE ID
16				15	14	13		12	11		10

DWG TYPE		PART DRAWING	
STYLE		DISTR CODE	D
VOLUME 10/1			
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE M-SCALE DIMENSIONING STANDARD (UNLESS OTHERWISE SPECIFIED) SEPARATE NOTATIONS OF FEATURES MAY BE BASED SEPARATELY PER M-SCALE OF REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION			
DO NOT SCALE			
USE MATH DATA			

DELPHI		DELPHI PACKARD ELECTRIC SYSTEMS	
WYOMING, WY			
DR		DATE	
APVD1	F. MIRANDA	25MY01	
APVD2	FCO, RESENDI	29MY01	
APVD3	ERIC TRACEY	31MY01	
APVD4			
APVD5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001			
MATERIAL SEE CHART			
DRAWING NAME			
TAXI MOUN BRKT CLIP			
DRAWING NUMBER			
12034026			
SIZE	SCALE	FRAME NO	SHEET NO
A0	2:1	1 OF 1	10 OF 10
STG	REV	N/P	
R	09	-	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15477667](#) [15477650](#) [15477668](#)