




SCALE 10:1



1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:  
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND  
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION  
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL  
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL  
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.  
ALL RADII 0.4  
DRAFT IS 1" ON ALL OUTSIDE SURFACES
2. TOOL CAVITY IDENTIFICATION SHOULD BE LOCATED AS CLOSE  
TO THE GATE AS POSSIBLE.
3. RECOMMENDED MATERIAL: GLASS REINFORCED  
NYLON OR POLYESTER.
4. WHEN USING THIS INFORMATION FOR A  
NEW DESIGN, REQUEST THE LATEST  
COPY OF THIS PRINT FROM PACKARD  
ELECTRIC DIV.

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:  
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND  
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION  
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL  
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL  
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. TOOL CAVITY IDENTIFICATION SHOULD BE LOCATED AS CLOSE  
TO THE GATE AS POSSIBLE.
3. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
4. MATING COMPONENTS OR EQUIVALENT:  
CONNECTOR 12059549  
TERMINAL 12015828
5. MATERIAL RECYCLING CODE >PP< PER SAE J1344. (2,31X(0,1) RAISED  
CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.  
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
6. (2,3X(0,1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY  
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.  
OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

		<div> <div>5</div> <div>PROCESS SENSITIVE DIMENSION</div> </div> <div>           DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED         </div>		ALL DIMENSIONS ARE IN MILLIMETERS REFERENCE	
<div>           DIMENSIONAL RANGE (MM)            FROM TO &gt; 0 &gt; 10 &gt; 20 &gt; 30 &gt; 40 &gt; 50 &gt; 60 &gt; 70 &gt; 80 &gt; 90 &gt; 100 &gt; 150 &gt; 200 &gt; 250 &gt; 300 &gt; 400            TOLERANCE ENCLOSED IN ( ) INDICATE TOLERANCE LIMITS ARE ESTABLISHED         </div>		CHART E1 TOLERANCE ENCLOSED IN ( ) INDICATE TOLERANCE LIMITS ARE ESTABLISHED		THIRD ANGLE PROJECTION	
SHARP CORNER TOLERANCE		DO NOT SCALE		USE DATA	

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM <sup>3</sup> )		DISTR CODE	
1.771		D	
ROUTING			
6900,6901			
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994			

<h1 style="text-align: center;">DELPHI</h1> <p style="text-align: center;">DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH</p>									
						DATE			
DR	G. MATLOCK					19F82			
APVD1	D. THIRY					25MR82			
APVD2	W. CROSS					30MR82			
APVD3	A. WINYARD					06AP82			
APVD4									
APVD5									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 1094R001									
MATERIAL M 2097003 PP IM GRA									
CONN 2 F M/P 480 GRA									
DRAWING NAME									
DRAWING NUMBER									
<div style="font-size: 2em; font-family: cursive;">12033701</div>									
SIZE	SCALE	FRAME		SHEET		NO	STG	REV	
AO	1:1	1 OF 1		1 OF 1		1		C2	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)  
[12033701](#)