





SYMBOL DEFINITION		MISSING SYMBOL	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	12
	LAST NO. USED		8

DATE		STG		REV		N/P		CHG		ZONE		REVISION HISTORY		AUTH		DR		APVD	
30JUL02	R	C3	-	-	-	-	-	-	-	-	-	REDRAWN TO PD, MAT'L SPEC WAS R0100151, ADDED NOTES 13 PLCS1, REVISED LOGO & RECYCLING CODE	226929	RCH	RH	1	2	1	2
16MR04	R	04	-	-	-	-	-	-	-	-	-	ADDED RADIUS TO LOCK 4 PLACES	253102	LMB	LMB	BG	BG	BG	BG
29MR04	R	04	AA	-	-	-	-	-	-	-	-	REVISED "PART ACCEPTS" NOTE TO "2.65 WIDE"	253521	ADK	ADK	BG	BG	BG	BG




1 NO FLASH ALLOWED IN THIS AREA, BOTH SIDES

OPTIONAL CONSTRUCTION

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE >PBT< PER SAE J1344. (11X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- MATING COMPONENTS OR EQUIVALENT: CONNECTOR 12064758
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: CAVITIES TO ACCEPT 12040993 TERMINAL OR EQUIVALENT. MAX INSULATION CRIMP MUST BE LESS THAN 3 HIGH AND 2.65 WIDE. SECONDARY TERMINAL LOCK 12047784
- THIS CONNECTOR WILL PASS THROUGH A 20.5 DIA MIN HOLE.
- (11X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.



DWG TYPE		PART DRAWING			
STYLE					
VOLUME (COP)	2,002	DISTR CODE	D		
ROUTING	6900				
UNLESS OTHERWISE SPECIFIED					
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2003 SUPPLEMENT TO Y14.5M-1994. DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.					
MATERIAL DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE USED SEPARATELY, REGARDLESS OF DATUM REFERENCE.					
ALL DIMENSIONS ARE IN MILLIMETERS					

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
OR	DATE
APVD1 ANDY T. LE	240C85
APVD2 F. HESTON	310C85
APVD3 S.A. NORLING	05N085
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL M4695002 PBT BLK	
DRAWING NAME	
CONN 3 M M/P 150 BLK	
DRAWING NUMBER	
12064759	
SIZE	SCALE
A0	5:1
FRAME NO	SHEET NO
1 OF 1	1 OF 1
REV	N/P
04	AA

5 PROCESS SENSITIVE DIMENSION		THIRD ANGLE PROJECTION		DO NOT SCALE	
DIMENSIONS ENCLOSED IN () INDICATE RETENTIVE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		USE MATH DATA		UNSUPP	
R 0.1 MAX		R 0.1 MAX		R 0.1 MAX	
R 0.2 MAX		R 0.2 MAX		R 0.2 MAX	
SHARP CORNER TOLERANCE		SHARP CORNER TOLERANCE		SHARP CORNER TOLERANCE	
DIMENSIONAL RANGE (MM)		DIMENSIONAL RANGE (MM)		DIMENSIONAL RANGE (MM)	
FROM		FROM		FROM	
TO		TO		TO	
TOLERANCE UNLESS OTHERWISE SPECIFIED		TOLERANCE UNLESS OTHERWISE SPECIFIED		TOLERANCE UNLESS OTHERWISE SPECIFIED	
ANGULAR TOLERANCE 12°		ANGULAR TOLERANCE 12°		ANGULAR TOLERANCE 12°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12064759](#)