





SYMBOL DEFINITION		MISSING NUMBERS	
THE NUMBER INSIDE THE SYMBOL  CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	25	
	LAST NO. USED	25	

DWG STATUS		ZONE		REVISION HISTORY		AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG					
27JA00	R	03	-	-	REDRAWN TO TQD, ADDED MATERIAL SAVERS	199255	EOV	QMC	OG
30AP02	R	03	AA	-	MAT'L SPEC WAS PM002233, ADDED LOGO NOTE & RECYCLING CODE NOTE & UPDATED PDM ATTRIBUTES	224496	JGR	EOV	ET



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- THIS PART IS CONTROLLED FOR AUTOMATIC FEEDING AS DENOTED ON DRAWING WITH .
- MATING COMPONENTS OR EQUIVALENT: CONNECTOR FUEL INJECTOR (ROCHESTER PRODUCT DIVISION P/N 05235126 REV (C) 1).
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: CAVITIES TO ACCEPT 12065453 TERMINAL
- MAXIMUM INSULATION CRIMP HEIGHT IS 2.72 AND WIDTH IS 3.9
- MATERIAL RECYCLING CODE >PA66< PER SAE J1344. (2.3)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

	DIMENSIONAL RANGE (MM)		CHART E1									
	FROM	TO	> 0.1	> 0.2	> 0.3	> 0.4	> 0.5	> 0.6	> 0.8	> 1	> 1.2	
TOLERANCE UNLESS OTHERWISE SPECIFIED												
SHARP CORNER TOLERANCE												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12065454](#)