










OPTIONAL CONSTRUCTION




NOTES


- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE >PBT< PER SAE J1344. (1.7)X(0.1) RAISED
CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- SEALING CODE 0 - (SEE ES-CD-50.5.1 FOR CODE EXPLANATION)
- MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 12110505
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 12110502
MAX INSULATION CRIMP MUST BE LESS
THAN 3 HIGH AND 2.6 WIDE.
SECONDARY TERMINAL LOCK 12047665
CONNECTOR POSITION ASSURANCE LOCK 12110503
- (0.9)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.
- NO CHANGE IS TO BE MADE TO THIS PART WITHOUT IFG AUTHORIZATION.

SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	15	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	9		

DWG STATUS				ZONE		REVISION HISTORY		AUTH		DR		APVD	
DATE	STG	REV	N/P	CHG									
03AP03	R	F5	-	-		REDRAWN TO PD; ADDED DELPHI LOGO & MATT'L RECYCLING CODE AS PREFERRED CONSTRUCTION AND REVISED MATT'L SPEC		238881	JGR	RH	ET		
07JA05	R	07	-	-		REVISED RADIUS ON INSIDE OF LOCK FEATURE		252625	JPB	JVM	BDG		



DIMENSIONAL RANGE (MM)											
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	CHART
TO	20	30	70	100	150	200	250	300	400		E1
TOLERANCE UNLESS OTHERWISE SPECIFIED											
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
ANGULAR TOLERANCE ±2°											

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM)		DISTR CODE	
2.549		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 PERFECT FORM AT MMC DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAUGED SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
		USE MATH DATA	
			

DELPHI									
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH									
DR J.M.SOVA								DATE	
APVD1 R.NOBLE								16OC90	
APVD2 R.NOBLE								20MY91	
APVD3 P.V.PALOVICH								06JN91	
APVD4								06JN91	
APVD5									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001									
MATERIAL M4698006 PBT GF30 YEL									
DRAWING NAME CONN 2 M M/P 150 YEL									
DRAWING NUMBER 12110504									
SIZE A2x3	SCALE 5:1	FRAME NO 1 OF 2	SHEET NO 1 OF 1	STG 1 R	REV 07	N/P -			

40201151

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12110504](#)