




MISSING SYMBOLS		DWG STATUS					ZONE	REVISION HISTORY		AUTH	DR	APPROV	
		DATE	SIG	REV	N/P	CHK						1	2
NO MISSING SYMBOL NUMBER	19AP99	R	01	-	-	CLEARED REV COLUMN & ALL PARTS - REDRAWN	192497	CRW	JRW	ET			
	19AP99	R	02	-	-	15355213 - RELEASED		990009	GRW	JRW	ET		
	08FE00	R	03	-	-	REVISED PROCESS NOTE #2		198547	SEP	SEP	ET		
	14JN04	R	04	-	-	12034329 & 15355213 - OBSOLETE AND ADDED NOTE 4		253207	JBD	JAA	SAN		
	04AU04	R	05	-	-	15495903, 15495904, 15495919 - RELEASED, ADDED PROCESS NOTES 4 & 5		257561	ADK	ADK	SAN		
	28MR05	R	06	-	-	ALL ACTIVE PARTS - DRAWING NAME (TAXI) MOUN CLAMP CDT		266203	CCV	JAA	TP		
	28OC05	R	07	-	-	12059394, 12084893 & 12103748 - OBSOLETE		273406	JTZ	JAA	PGD		
	23FE06	R	08	-	-	ADDED MAT'L SIZE, MAT'L SPEC & CONDUIT SIZE COLUMNS TO CHART AND REMOVED NOTE #4; 13576626 - RELEASED AND ADDED PROCESS NOTE #6		277573	JBD	JAA	TP		
	25AP06	R	09	-	-	13576626 - MAT'L SPEC WAS M0941X99		279475	RTV	FRG	TP		
	21AU06	R	10	-	-	13599110 - RELEASED		283852	RTV	AVJ	TP		
	17N006	R	11	-	-	13599110 - PROCESS NOTE WAS 7 15495903 - UPDATED PDM ATTRIBUTES		287026	GLB	FRG	TP		



TYPE 101 & 102

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:


DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. 0.15 HIGH BURR IS PERMISSIBLE EXCEPT AS NOTED.


3. DIMENSIONS OTHER THAN 3 PLACES SHOWN ON THIS
DRAWING ARE REFERENCE DIMENSIONS INTENDED
FOR TOOLING DESIGN CRITERIAL ONLY.

1. ZINC PLATE AND GOLD CHROMATE TREAT PER GM-4342-M
CODE 10D24 (POS-1065B-15)
2. PLATE PER GM4435-M, DK GREY, CODE A.
3. STALGUARD BLACK (DRY) MUST WITHSTAND
400 HOURS MINIMUM TO RED RUST IN
NEUTRAL SALT SPRAY, EXCEPT FOR "SHARP EDGES"
4. PLATE PER DX551318-P ZINC NICKEL WITH CLEAR TRIVALENT
CHROME AND TOPCOAT MUST WITHSTAND 400 HRS MINIMUM TO
RED RUST IN NEUTRAL SALT SPRAY.
5. PLATE PER DX550701-P ZINC PHOSPHATE WITH PROTECTIVE OIL
COMPOUND.
6. PLATING TO WITHSTAND 72 HRS. NEUTRAL SALT FOG SPRAY WITH
NO RED RUST ON ANY SURFACE, EXCEPT SHARP EDGES.
7. PLATING TO WITHSTAND 400 HRS. NEUTRAL SALT FOG SPRAY WITH
NO RED RUST ON ANY SURFACE, EXCEPT SHARP EDGES.

13591110	01	AA	-	0.6 X 19	M0929XXX-SAE 1008-1010 STRIP STEEL #3 TEMPER (QUARTER HARD TEMP) WITH NiZn PLUS PREPLATE	101	10.6 ±0.1	13.525 ±0.175	9.24 ±0.33	M10	25	6
13576626	01	AA	-	0.6 X 19	M0929XXX-SAE 1008-1010 STRIP STEEL #3 TEMPER (QUARTER HARD TEMP) WITH NiZn PLUS PREPLATE	102	6.4 ±0.1	9.4 ±0.1	11.34 ±0.33	M6	25	6
15495919	01	AA	-	0.6 X 19	#3 TEMPER 1008-1010 C.R. STEEL	101	10.6 ±0.1	13.525 ±0.175	9.24 ±0.33	M10	25	4
15495904	01	AA	-	0.6 X 19	#3 TEMPER 1008-1010 C.R. STEEL	102	6.4 ±0.1	9.4 ±0.1	11.34 ±0.33	M6	25	5
15495903	01	AB	-	0.6 X 19	#3 TEMPER 1008-1010 C.R. STEEL	101	10.6 ±0.1	13.525 ±0.175	9.24 ±0.33	M10	25	5
15355213	01	AB	OBsolete	0.6 X 19	#3 TEMPER 1008-1010 C.R. STEEL	103	6.4 ±0.1	9.4 ±0.1	11.34 ±0.33	M6	25	2
12103748	A3	-	OBsolete	0.6 X 19	#3 TEMPER 1008-1010 C.R. STEEL	101	10.6 ±0.1	13.525 ±0.175	9.24 ±0.33	M10	25	3
12084893	A4	-	OBsolete	0.6 X 19	#3 TEMPER 1008-1010 C.R. STEEL	102	6.4 ±0.1	9.4 ±0.1	11.34 ±0.33	M6	25	2
12059394	A4	-	OBsolete	0.6 X 19	#3 TEMPER 1008-1010 C.R. STEEL	101	10.6 ±0.1	13.525 ±0.175	9.24 ±0.33	M10	25	2
12034329	B2	-	OBsolete	0.6 X 19	#3 TEMPER 1008-1010 C.R. STEEL	101	10.6 ±0.1	13.525 ±0.175	9.24 ±0.33	M10	25	1
PART NO	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC	TYPE	gA	gB	C	HOLE SIZE ID	CONDUIT SIZE (MM)	PROCESS NOTE



6		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART	
FROM	0		
TO	12	> 12	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.1		±0.2	
ANGULAR TOLERANCE		±2°	

DRG TYPE	PART DRAWING		
STYLE			
VOLUME (OPT)	DISTR CODE		
			
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994 AS AMENDED BY THE 2018 SUPPLEMENT TO THE 2018 Y14.5-1994 ADDENDUM 0001. SEPARATE PATTERNS OF FEATURES BE USED SEPARATELY REMOVED OF DATA REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
12015679			
5	THIRD ANGLE PROJECTION	DO NOT SCALE	
0		USE MATH DATA	

DELPHI DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH									
						DATE			
DR									
APV01		CLAUDIA WYLER				13AP99			
APV02		JOSE HUERTA				27AP99			
APV03		ERIC TRACEY				27AP99			
APV04									
APV05									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001									
MATERIAL SHEET CHART									
DRAWING NAME:									
TAXI MOUN CLAMP CDT									
DRAWING NUMBER									
12059395									
SIZE	SCALE	FRAME	SHEET	NO	STO	REV	N/P		
A0	2:1	1 OF 1	1 OF 1	1	1	11	-		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15495903](#)