











SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	
	LAST NO. USED		
	34		
	25		

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
100C05	R	01	-	-		12092587 & 15496722 WERE SEPARATE DWG	271767	CCV	JVM	MLP



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 101



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- MATERIAL RECYCLING CODE PER ISO 11469. (2,3)X(0,1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- (2,3)X(0,1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED".
- THIS PART TO SNAP INTO 31.9±0.5 DIA HOLE IN 2 MAX THICKNESS STOCK.
- THIS PART TO FIT 6.25 DIA CABLE.

PART DRAWING	
STYLE	DATE
VOLUME (CM³)	DISTR CODE
SEE CHART	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 ADDENDUM-2018. SEPARATE PATTERNING OF FEATURES MAY BE GIVEN SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
APVD1 CESAR CERVANTES	190C05
APVD2 J. VILLAMIL	200C05
APVD3 MATT PENN	210C05
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEC. CHART	
DRAWING NAME	
TAXI LOCK STRAIN RLF	
DRAWING NUMBER	
13540380	
SIZE	SCALE
A0	2:1
FRAME NO	SHEET NO
1	1 OF 1
REV	N/P
01	-

(N/A) PROCESS SENSITIVE DIMENSION	
FROM	TO
0	20
20	30
30	70
70	100
100	150
150	200
200	250
250	300
300	400
TOLERANCE UNLESS OTHERWISE SPECIFIED	
1±0.15	±0.2
±0.3	±0.4
±0.5	±0.6
±0.8	±1
±1.2	±1.5
ANGULAR TOLERANCE 12°	

THIRD ANGLE PROJECTION	
DO NOT SCALE	USE MATH DATA
UNSPRINGS	

DIMENSIONAL RANGE (MM)	
FROM	TO
0	20
20	30
30	70
70	100
100	150
150	200
200	250
250	300
300	400
TOLERANCE UNLESS OTHERWISE SPECIFIED	
1±0.15	±0.2
±0.3	±0.4
±0.5	±0.6
±0.8	±1
±1.2	±1.5
ANGULAR TOLERANCE 12°	

PART NO		REV N/P		STATUS		TYPE		MATERIAL SPECIFICATION AND COLOR		VOLUME (CM³)	
15496722	01	AC		102		M2097003 PP 1M GRA		4.465			
12092587	06	AB		101		M2097001 PP 1M BLK		4.480			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15496722](#)