











Bild 1: Crimpversion >1-2.5mm²
Picture 1: Crimp version

		D		D		D														
B	12	6 001 36 44	B	13609245	01	>1.0-2.5	□□□	0.8μm Au ⁽⁷⁾	3.6	1.8	3.8	4.7	2.6	4.9	1.5	3.3	5.8	19.2	3.0	0.4
	11	6 001 44 42	---	---	---			3-5μm Ag												
	10	6 001 36 42	---	---	---			1.5-3 μm Ag												
	9	6 001 36 41	B	13609025	01			1-3μm Sn												
	8	6 001 36 34	B	13609247	01	0.5-1.0	□□	0.8μm Au ⁽⁷⁾	2.5	1.2	2.7	3.7	1.8	3.9	1.5	3.0	5.5	19.2	3.0	0.2
	7	6 001 44 32	---	---	---			3-5μm Ag												
6	6 001 36 32	---	---	---	1.5-3 μm Ag															
					1-3μm Sn															
A	5	6 001 36 31	B	13609027	01	0.2-0.35	□	0.8μm Au ⁽⁷⁾	1.9	0.8	1.9	2.5	1.0	2.5	1.7	2.5	5.3	18.8	3.4	0.2
	4	6 001 36 14	B	13609246	01			3-5μm Ag												
	3	6 001 44 12	---	---	---			1.5-3μm Ag												
	2	6 001 36 12	---	---	---			1-3μm Sn												
	1	6 001 36 11	B	13609026	01															
	Pos.	Teile Nr. Part no.	Rev.	Delphi Teile Nr. Part no.	Rev.	Crimp- bereich Crimp zone (mm ²)	Crimp- code	Ober- fläche Surface finish	B1 ±0.3	D1 ±0.3	(H1)	B2 ±0.3	D2 ±0.4	(H2)	A1 ±0.2	A2 ±0.2	A3 ±0.3	L1 ±0.5	L2 ±0.15	H3 +0.2




BILD 2: Crimpversion 0.2-0.35mm²
Picture 2: Crimp version

12-00227		-	Rev."D" - 11.02.2013: Error correction in the table: dimension no. 8 was 5.2 Table Notes kpl. redacted, ADDED: MWL rev. , Delphi part no and rev.	
018/09		-	Rev."C" - 07.01.2010: Hinzu: Angabe Produkt- / Crimpspezifikationsnr.	
ECN-NO. ECN-NUMBER		POSITION POSITION	CHANGE DESCRIPTION ÄNDERUNGSBESCHREIBUNG	
PRODUCT SPEC. PRODUKT-SPEZ.	PACKAGING SPEC. VERPACKUNGS-SPEZ.	APPLICATION SPEC. ANWENDUNGS-SPEZ.	COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD WITH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	DIESE ZEICHNUNG IST EIGENTUM DER FIRMEN DELPHI UND ENTÄHLT DELPHI VERTRAULICHE INFORMATIONEN. DIE REPRODUKTION, VERTEILUNG UND NUTZUNG DIESER DOKUMENTE ODER DERER ZUSAMMENGESETZTER DATENSÄTZE OHNE KENNZAICHEN VON DELPHI SIND UNTERSAGT. JEDE WEITERGEBUNG AN DRETTET, IST OHNE BERECHTIGENSPRUCH DURCH DIE DELPHI CORPORATION UNTERSAGT.
see Table	---	see table		
TOLERANCES TOLANZEN	DIN ISO 2768-FH DIN ISO 1101	MATERIAL : MATERIAL : siehe tabelle	SURFACE FINISH OBERFLÄCHE siehe Tabelle	CAD SYSTEM pro I eng.
COUNT PART NO. ZUGEWISSEN-Nr.	---	COLOUR : FARBE : siehe table	ECO Loc. Code STANDORT CODE GN	DWG SIZE FORMAT A2
DO NOT MEASURE DRAWING ZEICHNUNG NICHT VERMESSEN		TOOL NO. WERKZEUG-Nr.		DIMENSION IN MILLIMETERS BEMASSUNG IN MILLIMETER
	DATE DATUM	NAME NAME		
CREATED BY ERSTELLT	2002-07-03	S.WISS	non waterproof application	DRAWING NUMBER ZEICHN.- NUMMER 60013611C
MODIFIED BY GEÄNDERT	2014/03/10	Sylvia WEISS		REV. INDEX D
CHECKED BY GEPRÜFT	2014/03/10	St. MUELLER		APPROVAL LEVEL FREIGABESTUFE SHEET 1 of 1 row 1
APPROVED BY GENEHMIGT	2014/03/11	Franz PACHER	28 DCK Female Terminal	SCALE 2:
FILE NAME Date: 60013611C				See Table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[60013631](#) [60013641](#)