











12	11	10	9	8	7	6	5	4	3	2	1																												
SYMBOL DEFINITION A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.																																							
MISSING SYMBOLS TOTAL NO OF INSPECTIONS REQUIRED 5 NO MISSING SYMBOL NUMBER LAST NO. USED 5																																							
DWG STATUS DATE STG REV N/P CHG ZONE 20MY97 R A - - WAS PE059923 & RELEASED 970005 JCH RRS BG 28AU97 R B - - REVISED GRAPHICS 181871 JIL FKV BG 27N097 R C - - REVISED GRAPHICS 183226 EML RMM BG 27N097 R D - - REVISED GRAPHICS 184086 EML RMM BG 28JL08 R D1 - - REDRAWN TO PD & UPDATED MAT'L CALLOUT 405559 HRS ECB JPZ																																							
 																																							
 																																							
																																							
NOTES 1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: <p style="margin-left: 20px;">DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.</p> <p style="margin-left: 20px;">2. MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.</p> <p style="margin-left: 20px;">3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER NAP 4.10-18.</p> <p style="margin-left: 20px;">4. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.</p> <p style="margin-left: 20px;">5. (2.3)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED" OR NO LOGO.</p> <p style="margin-left: 20px;">6. FOR APPLICATION DATA SEE THE APPLICATION DRAWING.</p>																																							
 <p style="margin-left: 20px;">1 PROCESS SENSITIVE DIMENSION</p> <p style="margin-left: 20px;">DIMENSIONS ENCLOSED IN  INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED</p>																																							
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 20%;">DIMENSIONAL RANGE (MM)</td> <td style="width: 20%;">CHART E1</td> </tr> <tr> <td>FROM  0</td> <td>> 20</td> </tr> <tr> <td>TO  20</td> <td>> 30</td> </tr> <tr> <td></td> <td>> 30</td> </tr> <tr> <td></td> <td>> 70</td> </tr> <tr> <td></td> <td>> 100</td> </tr> <tr> <td></td> <td>> 150</td> </tr> <tr> <td></td> <td>> 200</td> </tr> <tr> <td></td> <td>> 250</td> </tr> <tr> <td></td> <td>> 300</td> </tr> <tr> <td></td> <td>> 400</td> </tr> <tr> <td colspan="2" style="text-align: center;">TOLERANCE UNLESS OTHERWISE SPECIFIED</td> </tr> <tr> <td colspan="2" style="text-align: center;">±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2</td> </tr> <tr> <td colspan="2" style="text-align: center;">ANGULAR TOLERANCE ±2°</td> </tr> </table>												DIMENSIONAL RANGE (MM)	CHART E1	FROM  0	> 20	TO  20	> 30		> 30		> 70		> 100		> 150		> 200		> 250		> 300		> 400	TOLERANCE UNLESS OTHERWISE SPECIFIED		±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2		ANGULAR TOLERANCE ±2°	
DIMENSIONAL RANGE (MM)	CHART E1																																						
FROM  0	> 20																																						
TO  20	> 30																																						
	> 30																																						
	> 70																																						
	> 100																																						
	> 150																																						
	> 200																																						
	> 250																																						
	> 300																																						
	> 400																																						
TOLERANCE UNLESS OTHERWISE SPECIFIED																																							
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2																																							
ANGULAR TOLERANCE ±2°																																							
 <p style="margin-left: 20px;">THIRD ANGLE PROJECTION</p> <p style="margin-left: 20px;">DO NOT SCALE</p> <p style="margin-left: 20px;">USE MATH DATA</p> <p style="margin-left: 20px;"></p>																																							
DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH																																							
DWG TYPE PART DRAWING STYLE VOLUME (DM) 11.820 DISTR CODE  UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAUGED SEPARATELY REGARDLESS OF DATUM REFERENCES.																																							
ALL DIMENSIONS ARE IN MILLIMETERS REFERENCE MATERIAL POLYAMIDE COMPOUND BLACK																																							
DRAWING NAME CONN 16 M M/P 280 DRAWING NUMBER 15326242 SIZE A1 SCALE 2:1 FRAME NO 1 OF 1 SHEET NO 1 OF 1 STG D1 REV N/P																																							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15326242](#)