





① BEMERKUNGEN / NOTES
 ② MVL-FIRMENZEICHEN / MVL-SUPPLIER CODE
 ③ CRIMP- CODE / CRIMP CODE
 MASS GILT NUR FÜR KABELKONFEKTIONÄR
 DIMENSION ONLY FOR HARNESSMAKER
 ABWEICHUNGEN VON DER BILDLICHEN DARSTELLUNG
 SIND IM BEREICH DER ÜBERFEDER ZULÄSSIG
 DEVIATIONS FROM THE FIGURATIVE REPRESENTATION
 ARE PERMISSIBLE IN THE RANGE OF HOOD
 SPULEN HORIZONTAL TRANSPORTIEREN UND LAGERN!
 HALTESTREIFEN UNTEN!
 REELS TRANSPORTED AND STORED HORIZONTAL! RETAINING
 STRIP DOWN!
 ZUGEHÖRIGE KAMMER / REFERENCE CAVITY:
 9 001 07 00
 FÜR LEITUNGEN / FOR CABLE: FLRY DIN 72551-6
**ÄNDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN
 BEHALTEN WIR UNS VOR ! I CHANGES BASED ON TECHNICAL
 PROGRESS ARE IN THE DECISION OF THE MANUFACTURER !**

6 011 06 14 6 011 06 34 6 011 06 44	A3	1-3µm Sn ALLSEITIG / ALL SIDES
	A2	MIN. 0.8µm AuCo 0.3 UEBER / OVER 1.3-2µm Ni
	A1	0.5µm Ni ALLSEITIG / ALL SIDES
6 011 06 11 6 011 06 31 6 011 06 41	A1	1-3µm Sn FEUERVERZINNT/HOT TIN
TEILE-NR. PART NO.	MASS DIMENSION	OBERFLAECHE SURFACE FINISH

6 011 06 44	33522389	0.8µm Au	>1.0-2.5	□□□	3.6	3.8	0.9	4.7	4.9	1.3	3.3	5.8	0.4	BAND EN 1654 CuSn4 R480	KALTBAND EN 10258 STAHL EN 10151- X10CrNi18-8
6 011 06 41	10756896	1-3µm Sn												BAND EN 1654 CuFe2P R420	
6 011 06 34	10779250	0.8µm Au	0.5-1.0	□□	2.5	2.7	0.6	3.7	3.9	0.9	3.0	5.5	0.2	BAND EN 1654 CuSn4 R480	
6 011 06 31	10774272	1-3µm Sn												BAND EN 1654 CuFe2P R420	
6 011 06 14	33500679	0.8µm Au	>0.20-0.35	□	2.1	2.1	0.4	2.7	2.8	0.7	2.5	5.6	0.2	BAND EN 1654 CuSn4 R480	
6 011 06 11	10774271	1-3µm Sn												BAND EN 1654 CuFe2P R420	
MVL TEILE-NR. MVL PART NO.	DELPHI TEILE-NR. DELPHI PART NO.	OBERFLÄCHE SURFACE FINISH	CRIMPGRÖSSE CRIMP SIZE (mm²)	CRIMP- CODE	B1 ±0.3	(H1)	R1 ±0.2	B2 ±0.3	(H2)	R2 ±0.2	E1 ±0.2	F ±0.5	G +0.2	GRUNDKÖRPER CONTACT BODY	UEBERFEDER HOOD
															MATERIAL

14-10262 17.11.14 F ABII DELPHI P/N ADDED 1 1 1 1 1 1 432/07 14.08.07 E02 - ERSTELLUNG IN PRO-E 1 1 1 1 1 1 ECN-NO. ECN NUMBER DATE DD / MM / YY REVISION INDEX POSITION POSITION CHANGE DESCRIPTION ÄNDERUNG DRAWN BY GEZ. CHK. BY GEPR. APPR. BY GEN.										PRODUCT SPEC. PRODUCT SPECIFIK. --- --- PACKAGING SPEC. VERPACKUNGSSPECIFIK. --- --- APPLICATION SPEC. ANWENDUNGSSPECIFIK. 9 084 11 00 --- COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MAIN DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED. ---										TOLERANCES DIN 2768-tm TOLERANZEN DIN ISO 1101 MISSE 0,3; 0,05 COUNTERPART Nr. GLEICHSTÜCK Nr. --- DO NOT SCALE DRAWING ZEICHNUNG NICHT VERMESSEN DRAWN BY GEZ. 14.08.07 S.Weiss CHECKED BY GEPR. 14.08.07 S.Mueller APPROVED BY 14.08.07 M.Hopf										MATERIAL: MATERIAL: --- COLOUR: FARBE: --- TITLE BENENNUNG FLACHSTECKER 2.8 - DCS2 NORMALE ANWENDUNG MALE TERMINAL 2.8 - DCS2 NORMAL APPLICATION										SURFACE FINISH OBERFLÄCHE --- ECO Loc. Code STANDORT CODE GN										DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE NUMERBERS GERMANY ISO PROJECTION ISO PROJEKTION DIMENSION IN MILLIMETERS MESSUNG IN MILLIMETER PROJ. SIZE FORMAT A2										CAD SYSTEM --- SHEET BLATT 1 FILE NAME DATE / NAME 60110611C.E02 SCALE 1:1									
---	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[60110614](#) [60110631](#) [60110641](#) [60110611](#) [60110634](#)