



SYMBOL DEFINITION			MISSING SYMBOLS
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	4	NO MISSING SYMBOL NUMBER
	LAST NO. USED	4	

DWG STATUS					ZONE	REVISION HISTORY				AUTH			
DATE	STG	REV	N/P	CHG									
27JN03	R	01	AA	-		REDRAWN TO PD				237786	FKV	FKV	JH
130C03	R	02	-	-		REVISED GRAPHICS				247034	AMG	AMG	JH
11MR04	R	03	-	-		36.3 ±0.2 WAS 36.3 ±0.15; 17.3 ±0.2 WAS 17.3 ±0.15				251671	ADK	ADK	JH



ACHTUNG!
In der Mercedes-benz AG nicht
übliche Darstellungsmethode

CAUTION!
Method not common at
Mercedes-Benz AG



ACHTUNG!
In der Mercedes-benz AG nicht
übliche Darstellungsmethode

CAUTION!
Method not common at
Mercedes-Benz AG

Lieferung nur nach Zeichnung und/oder CAD-Daten sowie erprobtem, freigegebenem Muster. Keinerlei Änderung ohne vorherige Freigabe durch die mit Aenderungsvermerk der DaimlerChrysler AG versehene (n) Zeichnung/CAD-Daten. Delivery only in accordance with drawing and/or CAD data, and tested and approved sample. No change without advance approval by the drawing/CAD data identified with the modification note by DaimlerChrysler AG.

Lf./And/Supp.rev.	Lf./Supp.	Gewicht (kg)	CAD	ZGS	ED-KB
		Weight			
Prüfer/Checker	Datum/Date	Norm/Standard	Datum/date	Abt./Dept.	Name
				AAV/EF	Datum/Date
Daimler-Benz Benennung/Title					
Mercedes-Benz Sach-Nr./Basic number			System		Format
					Blatt/Sheet


Ab/As of 1998-12-21
neuer Firmenname
new company name
DaimlerChrysler AG

NOTES



- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATING COMPONENTS OR EQUIVALENT:
CONN 34 F MQS MCP 15440138

MATERIAL NOTES

- MATERIAL: SILICON, AUTOLUBRICATION
TENSILE: RM MIN 6.2 N/mm²
ELONGATION: 375% DIN 53504-S2
DUROMETER ORIGINAL: SHORE (A) 50 ±5 DIN 53505
MEASURE ON TEST SLABS
COLOR: RED-BROWN



2 PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART E
FROM 0 TO 20	> 20 > 30 > 70 > 100
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.15 ±0.2 ±0.3 ±0.4 ±0.5	
ANGULAR TOLERANCE ±2°	

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)		DISTR CODE	
0.872			
ROUTING			
6901			
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
		USE MATH DATA	

DELPHI

DELPHI PACKARD ELECTRIC SYSTEMS
WARREN, OH

DR		DATE				
APVD1	F/TRAN	11SE02				
APVD2	YILDIZ	11SE02				
APVD3	R.WIS.	30SE02				
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001						
MATERIAL SEE NOTES						
DRAWING NAME						
SEAL CONN HSG RST						
DRAWING NUMBER						
15426733						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A2	2:1	1 OF 1	1 OF 1	R	03	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15426733](#)