



SYMBOL DEFINITION				MISSING SYMBOLS				DWG STATUS				REVISION HISTORY				AUTH			
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.				TOTAL NO OF INSPECTIONS REQUIRED				DATE				DATE				DATE			
LAST NO. USED				21				10JUN04				R 01 - -				255860			
				18								RELEASED				ADM/ADM/RAP			

THIS AREA MUST BE FLAT TO WITHIN
1.30 MM TOTAL AND FREE FROM
SURFACE DEFECTS AT LEAST 7.0 MM
ALL AROUND









BODY MOUNTING HOLE

THIS AREA MUST BE FLAT TO WITHIN
1.30 MM TOTAL AND FREE FROM
SURFACE DEFECTS AT LEAST 7.0 MM
ALL AROUND











DOOR MOUNTING HOLE



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
3. MATING COMPONENTS OR EQUIVALENT:
CONNECTOR ASSEMBLY 15479759 OR EQUIVALENT (BODY END)
4. PART IS SYMMETRICAL ABOUT CENTERLINES EXCEPT AS NOTED.
5. SEALING SURFACES MUST BE FREE OF SINKS, NFO'S, VOIDS,
KNIT/FLOW LINES, ETC.
6. MATERIAL NOTES - (BLACK):
ASTM D-2000 M3BAS10 A14 B13 C12 F17 Z1 Z2 Z3
Z1=100% EPDM
Z2=STAIN RESISTANCE (D-925-88 METHOD B)
Z3=TEAR RESISTANCE (DIE B=35 kN/m MIN)
(DIE C=30 kN/m MIN)

DRAWING NUMBER			
15484457			
SIZE	SCALE	FRAME NO	SHEET NO
A1x3	1:1	2 OF 2	1 OF 1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15484457](#)