

16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

M L K J H G F E D C B A

VIEW TO Y-Y

(1) 7.4 ±0.2

(2) (23.82)

Y

Y

(7) E ±0.4

VIEW TO Y-Y

TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN

(4-5) 2X (14.77) TYP

(3) 4 MAX EXCLUDING COIN

(6) +0.15
-0.1

TYPE 101

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- RECOMMENDED MATING BLADE 0.81 THK X 6.3 WIDE
- DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
- FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER, TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE PERFORMANCES OF THE PART.

VIEW SCALE DOES NOT REFLECT ACTUAL PART SIZE

(B)

PART NO	REV	N/P	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	SIZE (MM²)	ID	CABLE	TYPE	E
15366082	O1	AC	0.406 X 38.1			AG PLATED COPPER ALLOY	2 - 1	15	3.97 - 2.48	101	3.7	
12052064	D2	--	0.406 X 38.1			TIN PLATED COPPER ALLOY	2 - 1	15	3.97 X 2.48	101	3.7	
12047569	E3	--	0.406 X 38.1			TIN PLATED COPPER ALLOY	0.8 - 0.5	19	3.12 - 2.03	102	3.2	
12041204	D	--	0.406 X 43.26			TIN PLATED COPPER ALLOY	2 - 1	15	3.97 - 2.48	101	3.7	

UNPLATED

PLATED

SIZE AD

SCALE 10:1

FRAME NO 1

SHEET NO 1 OF 1

STG REV N/P

REV I/P

R 04

SYMBOL DEFINITION

THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER

TOTAL NO. OF SYMBOLS ON DRAWING

LAST NO. USED

MISSING NUMBERS

DWG STATUS

DATE STG REV N/P CHG ZONE

REVISION HISTORY

AUTH DR APVD/APV

15366082 - RELEASED;
12052064 & 12047569 WERE SEPARATE DWG

990005 LMM JHY HJR

11DE02 R 02 - - UPDATED PDM ATTRIBUTES

229867 JFN EAR B6

24MY06 R 03 - - ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES

280890 JTZ JAA BDG

19FE15 R 04 - - 15366082 - ADDED TARNISH INFO NOTE

428877 ABH JVM JSW

DELPHI

DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE

WARREN, OH

COPYRIGHT 1999 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DATE

DR

APV01 L. MACIAS

22MR99

APV02 JOSE HUERTA

12AP99

APV03 JOSE HUERTA

12AP99

APV04

APV05

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (094990)

MATERIAL

SEE CHART

DRAWING NAME

TAXI TERM F/WP 630 SPL

DRAWING NUMBER

12045886

SIZE AD

SCALE 10:1

FRAME NO 1

SHEET NO 1 OF 1

STG REV N/P

R 04

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

PROCESS SENSITIVE DIMENSION

DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

DIMENSIONAL RANGE (MM)

FROM 0 TO 12

CHART C2

> 12

TOLERANCE UNLESS OTHERWISE SPECIFIED

±0.1

±0.2

ANGULAR TOLERANCE ±2°

REFERENCE

LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT DELPHI SALES TO ASSURE AVAILABILITY OF PARTS.

DWG TYPE

PART DRAWING

STYLE

VOLUME (OMP)

DISTR CODE

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING HANDBOOK - (1997). ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY PER RULE #1 (PRECEPT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE BASED SEPARATELY, REGARDLESS OF DATUM REFERENCE.

ALL DIMENSIONS ARE IN MILLIMETERS

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

NX

11-Nov-15 Time: 08:31

Part : 12045886-CUS01-S01

Page:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12052064-L](#)