



SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	10
	LAST NO. USED	10

MISSING SYMBOLS
NO MISSING SYMBOL NUMBER

DWG STATUS					ZONE		REVISION HISTORY		AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG								
09JN03	R	01	-	-			WAS PE117888 AND RELEASED		242303	ECB	AUG	GCD
100C03	R	02	-	-			ADDED RIB; REVISED MATERIAL RECYCLING CODE NOTE		247227	ADK	BB	GCD
210C03	R	03	-	-			REVISED MODEL & UPDATED PDM ATTRIBUTES		247594	EES	EES	GCD
270C03	R	03	AA	-			REVISED MODEL & UPDATED PDM ATTRIBUTES		247995	EES	EES	GCD
19FE04	R	04	-	-			UPDATED MAT'L M3592018 WAS M3592025; REVISED NOTE, LOCK, STRAP AND DIM B.		252172	DAD	DAD	GCD
14AP04	R	04	AA	-			REVISED DIMS & NOTE IN TOD		253847	LMB	LMB	GD
19AP04	R	04	AB	-			REVISED PRINT TO MATCH PART		254185	RH	RH	GCD
21AP04	R	04	AC	-			ADDED FLASH NOTE		254306	MAC	MAC	GCD
10SE04	R	04	AD	-			UPDATED FORMAT AND PDM ATTRIBUTES		258911	BRB	BRB	GCD
22SE04	R	04	AE	-			PART OBSOLETE, REPLACED BY 13512189		259436	LMB	LMB	GCD
09DE04	R	04	AF	-			REINSTATED & UPDATED PDM ATTRIBUTES		261828	JTV	FKV	GCD
26SE05	R	05	-	-			REVISED MODEL AND UPDATED PDM ATTRIBUTES		272217	EES	EES	GCD
06JA06	R	05	AA	-			ESDS3054503/03 WAS S3054531/01		276154	CJP	CJP	GCD



NOTES


- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (1.5)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
- (1.5)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED".
- THIS CABLE TIE IS DESIGNED TO BE USED WITH A T5 WELD STUD.

ASSEMBLY PROCESSING NOTES:

- PART CAN BE USED WITH HARNESS DIAMETER UP TO A MAX OF 28MM TAPED OR 22MM CONDUIT AND A MIN DIA OF 4MM.
- APPLY TO HARNESS WITH PANDUIT GUN GS2B (MANUAL). GUN TO BE SET AT "STD" AND A TENSION OF 6-8.

7	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	

DIMENSIONAL RANGE (MM)										CHART	E1
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300		
TO	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED											
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2											
ANGULAR TOLERANCE ±2°											

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CNP)		DISTR CODE	
2.437		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
			
USE MATH DATA			

DELPHI									
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH									
DR							DATE		
APVD1		E.A. CACHO					17JN03		
APVD2		A UGALDE G					18JN03		
APVD3		GARY C. DETTER					19JN03		
APVD4									
APVD5									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001									
MATERIAL M3592018 PA66 HS IM GRA DRK									
DRAWING NAME MOUN WIRE TIE CLIP HD PUSH NUT M6									
DRAWING NUMBER 15465829									
SIZE A1	SCALE 1:1		FRAME NO 1 OF 1		SHEET NO 1 OF 1		STG R	REV 05	N/P AA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15465829-B](#)