


MISSING SYMBOLS		DWO STATUS					ZONE	REVISION HISTORY	AUTH	RD	APVD	APVD2
		DATE	STG	REV	N/P	CHG						
NO MISSING SYMBOL NUMBER		30JUL02	R	07	-	-	CLEARED REVISION COLUMN; ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES	226419	ECB	JAA	TTP	
		17JUL03	R	08	-	-	15369260, 15304708, 15304705, AND 15304704 - ADDED TERMINAL MAKE STRAIGHTNESS AND TERMINAL CRIMP STRAIGHTNESS VIEWS. DRAWING SIZE WAS A1. REVISED LOCAL NOTE.	242518	BRB	BRB	MC	
		07COC3	R	09	-	-	15304705 - UPDATED PDM ATTRIBUTES	246958	EES	EES	AD	
		07FE04	R	10	-	-	ALL ACTIVE PARTS - REMOVED 0.75#0.75 & 2X 21.3 MAX TIP DIMS; DIM #7 WAS #24 & DIM #24 WAS #28	251682	TLT	LDL	MCJ	
		04COC04	R	11	-	-	15304704-05, 15304708 & 15369260 - ADDED STAMP DIE 1-D	259308	CTR	JVM	MMK	
		01DE08	R	12	-	-	ALL ACTIVE PARTS - UPDATED MATERIAL CALLOUT	406827	WH	HC8	WH	
		1BMRI0	R	13	-	-	ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES	410262	JTZ	JTZ	MAC	
		06AUI0	R	14	-	-	ALL ACTIVE PARTS - ADDED PLATING NOTE, UPDATED MAT'L CALLOUT AND ADDED CONTACT AREA & CRIMP AREA COLUMNS ON CHART	411494	C8B	C8B	VMR	
		06COC10	R	15	-	-	ALL ACTIVE PARTS - UPDATED PLATED NOTES	412129	C8B	C8B	VMR	
		10AUI1	R	16	-	-	ALL ACTIVE PARTS - ADDED PREFERRED MAT'L SIZE COLUMN AND UPDATED PDM ATTRIBUTES	415106	JAR	JAR	DAF	
		03OC12	R	17	-	-	1369180 - RELEASED	419883	CER	CER	JFF	




SCALE 2:1



SCALE 2:



SCALE 2:1



SCALE 2:1

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.




2. MATING COMPONENTS OR EQUIVALENT:
TERMINAL 12191816.

4. PLATING TYPE:
1. REFLOW TIN 1.9 - 3.3 MICROMETERS THICK WITH A COPPER UNDERPLATE 0.5 MICROMETER TO 1.0 MICROMETER THICK.

PLATING TYPE INFORMATION SHOWN ABOVE IS REFERENCE ONLY.
PLATING REQUIREMENTS ARE CONTAINED IN APPLICABLE
MATERIAL SPECIFICATION.

PART NO	REV	N/P	PREFERRED MAT'L SIZE	ALTERNATIVE MAT'L SIZE	MAT'L DESCRIPTION	SIZE (MMF)	ID	DIA	TYPE	B _{1,0.2}	(L)	REPLACED BY	RESTRICTED USAGE	CONTACT AREA PLATING TYPE (BUTTE)	CRIMP AREA PLATING NOTE
17969180	01	-	0.3 X 35.75	0.3 X 36.12	COPPER ALLOY	1.5 - 2.5	14	3.0 - 2.2	101	3.75	28.15	-	-	I	I
15369260	01	AK	0.3 X 35.75	0.3 X 36.12	COPPER ALLOY	1 - 1.5	15	2.4 - 1.9	101	2.95	28.15	-	RESTRICTED	I	I
15304708	E10	-	0.3 X 35.75	0.3 X 36.12	COPPER ALLOY	1 - 1.5	15	2.4 - 1.9	101	2.95	28.15	-	RESTRICTED	I	I
15304707	E1	-	-	0.3 X 36.12	COPPER ALLOY	0.75 - 1	17	2.25 - 1.7	101	2.65	28.15	15326269	-	I	I
15304706	E11	-	-	0.3 X 36.12	COPPER ALLOY	0.35 - 0.5	21	1.85 - 1.2	101	2.1	28.15	15326268	-	I	I
15304705	F1	-	0.3 X 35.75	0.3 X 36.12	COPPER ALLOY	0.75 - 1	17	2.25 - 1.7	101	2.65	28.15	-	-	I	I
15304704	F10	-	0.3 X 35.75	0.3 X 36.12	COPPER ALLOY	0.35 - 0.5	21	1.85 - 1.2	101	2.1	28.15	-	-	I	I

5		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART	
FROM 0			
TO 12			> 12
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.1		±0.2	
ANGULAR TOLERANCE		±2°	

<p>LINE DROPPED THROUGH A PART NUMBER INDICATES THAT PARTS ARE NOT AVAILABLE FOR ORDERING.</p> <p>PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PARTS ARE AVAILABLE FOR ORDERING.</p> <p>CONTACT DEALER SALES TO ASSURE AVAILABILITY OF PARTS.</p>	
<p>DWG TYPE</p> <p>PART DRAWING</p>	
<p>STYLE</p>	<p>DISTR CODE</p>
<p>UNLESS OTHERWISE SPECIFIED</p> <p>THIS DOCUMENT IS IN ACCORDANCE WITH ANSI Y14.9-1994 STANDARD FOR FIRST ANGLE PROJECTION AND TOLERANCE STACKING. SEPARATE PARTS OF DRAWINGS SHOULD BE USED SEPARATELY. PEEVISHNESS OF DATUM REFERENCE.</p>	
<p>ALL DIMENSIONS ARE IN MILLIMETERS</p>	
<p>REFERENCE</p>	
<p>PROJ ANGLE THIRD ANGLE</p> 	<p>DO NOT SCALE</p>  <p>USE MATH DATA</p> 

<div>DELPHI</div> <div>DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE</div> <div>WARREN, OH</div> <div>COPYRIGHT 1996 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.</div> <div>THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. NO REPRODUCTION, EITHER WHOLLY OR IN PART, OR USE OF THIS DOCUMENT OR ITS RELATED CAD DATA, FOR ANY USE, WITHOUT PERMISSION OF DELPHI CORPORATION, IS FORFEIT. NO COMMUNICATION OF PAY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.</div>									
DR					DATE				
AP001 N. VERGARA					05FE96				
AP002 SIEGLE					08JUN96				
AP003 S.S HSIEH					28JUN96				
AP004									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 12943901									
MATERIAL SHEET CHART									
TAXI TERM M GT 150 SEALED									
DRAWING NUMBER									
15304703									
SIZE		SCALE		FRAME NO		SHEET NO		STG REV N/P	
A0		1:1		1 OF 1		1 OF 3		R 17	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15304704-L](#)