




SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	7	5-6	
	LAST NO. USED	9		

DWG STATUS					ZONE	REVISION HISTORY		AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P	CHG							
21JA02	R	01	-	-		CLEARED REVISION COLUMN AND ALL PARTS - REVISED GRAPHICS		213978	AMG	AMG	JL
10JN05	R	02	-	-		ADDED PROBING NOTE		269172	AKJ	AKJ	WTM
100C05	R	03	-	-		15324339 & 15324340 - UPDATED PDM ATTRIBUTES		273333	JBD	AUG	EJH
18JA06	R	04	-	-		15324339-41 - UPDATED MAT'L SPEC & REVISED CABLE O.D 13572757, 13572763-64 - RELEASED		276448	JTV	AUG	WTM
02FE06	R	05	-	-		13572764 - CABLE GAGE ID WAS 10, ADDED 3 TO CABLE SIZE & UPDATED PDM ATTRIBUTES; 13572757 & 13572763 - UPDATED PDM ATTRIBUTES		276999	JTV	AUG	WTM
10MR06	R	06	-	-		15324339 & 15324341 - UPDATED PDM ATTRIBUTES		276499	JTV	AUG	JS
16MR06	R	07	-	-		ALL PARTS - REMOVED DIM(S) 5 & 6, ADDED DIM(S) 7, 8 & 9 FROM TOD; 13572764 - UPDATED CABLE DIA		278352	CCV	FKV	WTM
01AP09	R	08	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES		407701	JTZ	FKV	WTM
160C09	R	09	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES; 13791853 - RELEASED AND ADDED VIEW TYPE 102		409229	HCG	AUG	WTM
21DE09	R	10	-	-		13791853 - DIM E WAS 5.8, CABLE SIZE WAS 4 - 6		409673	JAR	JAR	WTM
11MY10	R	11	-	-		13572764 - CABLE DIA WAS 3-5.33; 13791853 - CABLE DIA WAS 3.49-5.24		410798	JTZ	JTZ	WTM
28JL11	R	12	-	-		13572764 - ADDED CRIMPED ONTO 5 MM² NOTE		414952	JCF	JVM	WTM
18JL13	R	13	-	-		33106900 - RELEASED		423294	ORA	JVM	JSM
07FE14	R	14	-	-		33106900 - SIZE (MM²) WAS 0.35 - 2		425431	APB	JVM	JFS
19FE15	R	15	-	-		13572757, 13572763-64 & 13791853 - ADDED TARNISH NOTE		428876	JVR	JVM	JSM



TYPE 101



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- RECOMMENDED MATING BLADE - WITH 2.8 ±0.08 THICKNESS 0.825 ±0.035
- DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
- TERMINAL 13572764 WHEN CRIMPED ONTO 5MM² 105 STRAND CONDUCTOR, CONDUCTOR WINGS MUST BE SOLDERED.
- FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER, TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE PERFORMANCE OF THE PART.

33106900	01	AA	0.406 X 32.54	SN PLATED COPPER ALLOY	0.35 - 0.8	-	1.3-2.1	101	3	4.7	0.5
13791853	02	AB	0.406 X 32.54	AG PLATED COPPER ALLOY	4 - 5	10	3.4-5.24	102	5.4	7.6	1
13572763	01	AE	0.406 X 32.54	AG PLATED COPPER ALLOY	3	12	3-3.81	101	4.6	6	0.7
13572764	01	AG	0.406 X 32.54	AG PLATED COPPER ALLOY	3 - 5	11	3-4.09	101	4.6	7.6	1
13572757	01	AE	0.406 X 32.54	AG PLATED COPPER ALLOY	1 - 2	15	2.05-3.43	101	3.7	6	0.7
15324341	02	AF	0.406 X 32.54	SN PLATED COPPER ALLOY	3	12	3-3.81	101	4.6	6	0.7
15324340	02	AF	0.406 X 32.54	SN PLATED COPPER ALLOY	3 - 5	11	3-5.33	101	4.6	7.6	1
15324339	02	AG	0.406 X 32.54	SN PLATED COPPER ALLOY	1 - 2	15	2.05-3.43	101	3.7	6	0.7
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	SIZE (MM²)	ID	DIA	TYPE	E	F	L
PLATED				CABLE							

3 PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART D
FROM 0	>12
TO 12	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.1	±0.2
ANGULAR TOLERANCE ±2°	

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT DELPHI SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	
VOLUME (QNP)	DISTR CODE
	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	NX

DELPHI	
DELPHI CORPORATION TROY, MI 48068 COPYRIGHT 1998 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR	DATE
APVD1 MANUEL VEGA	22JN98
APVD2 MANUEL VEGA	22JN98
APVD3 O. GALLEGOS	27AU98
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHART	
DRAWING NAME	
TAXI TERM F M/P 280	
DRAWING NUMBER	
15324365	
SIZE A1	SCALE 10:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV 15
N/P	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15324339-L](#) [15324340-L](#)