


TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 108
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 111
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 106
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 109
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 112
SAME AS TYPE 101
EXCEPT AS SHOWN








TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 107
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 110
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 113
SAME AS TYPE 101
EXCEPT AS SHOWN

SYMBOL DEFINITION		TOTAL NO OF INSPECTIONS REQUIRED		LAST NO. USED	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.		20		5	



TYPE 101



CLOSED CAVITY

OPEN CAVITY

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATING DEVICE COMPONENTS OR EQUIVALENT: SEE 15454981 FOR CASE/HEADER MATING PART INFORMATION SEE CHART FOR MALE SERVICE CONNECTOR.
- SEALING CODE 4 - DESIGN WILL MEET REQUIREMENTS OF SAE/USCAR-2 CONNECTOR SYSTEM ENVIRONMENTAL TEST FLOW CHART (PRESSURE/VACUUM AND SUBMERSION).
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: TERMINAL: 15359001 CABLE O.D. RANGE: 1.45/2.20 DIA CONNECTOR POSITION ASSURANCE: 15318055 SECONDARY LOCK: 15455458
- ASSEMBLY TO BE USED WITH APPROPRIATE DELPHI PACKARD ELECTRIC HOLDER DESIGNS.
- ASSEMBLY TO BE PROCESSED USING DELPHI PACKARD ELECTRIC SYSTEMS BEST PRACTICE METHODS AND/OR CONNECTOR ASSEMBLY INSTRUCTIONS, AND APPLICABLE REPAIR PROCEDURES.

PART NO	REV	N/P	TYPE	STATUS	CABLE SEAL	MATING MALE SERVICE CONNECTOR ASM	PUNCHED HOLE PATTERN (OPEN CAVITIES)
15491247	01	AA	113	-	15491246	TBD	4-9,14-16,18
15480014	01	AB	109	OBSOLETE	15480012	TBD	1,3-9,14-16
15476743	02	-	112	-	15476742	TBD	1,4-7,14-17
15476593	02	AA	111	-	15476592	TBD	1,2,4-7,9-10,14-16
15473133	04	AA	110	-	15473132	TBD	4-9,14-17
15475197	02	AA	108	-	15472512	TBD	4-7,9,14-16,18
15475196	02	AA	107	-	15445953	TBD	1-18
15475195	02	AA	106	-	15447999	TBD	4-9,14-18
15455462	02	AB	105	OBSOLETE	15439425	15445243	2,4-9,11,14-16
15455461	02	AA	104	-	15439422	15445242	1-9,11,14-16
15455460	02	AA	103	-	15439421	15445241	4-9,14-16
15475194	02	AA	102	-	15439463	TBD	1,2,4-7,9-11,14-16,18
15475193	02	AA	101	-	15439462	TBD	1,2,4-7,9,14-16,18

DWG STATUS				ZONE				REVISION HISTORY				AUTH			
DATE	STG	REV	N/P	CHG											
25MR03	R	01	-	-				ALL PARTS - PART DRAWING CREATED				238518	JVM	JVM	PD
08JUL03	R	02	-	-				CHANGED TYPE* REFERENCE FOR P/N* 154955460, 154955461, 154955462, 15475193, 15475194, 15475195, 15475196, 15475197, 15473133.				243318	SS	SS	PD
03SE03	R	03	-	-				15476593 - RELEASED				245300	MAC	MAC	PD
14OC03	R	04	-	-				ALL PARTS- NOTE 4 CABLE O.D. RANGE: 1.45/2.20 DIA WAS 1.45/2.45 DIA, REVISED STRAIN RELIEF 15448000. 15473133 WAS TYPE 109, 15476593 WAS TYPE 110; RELEASED - 15476743 & 15480014				246550	CJP	CJP	PD
17DE03	R	05	-	-				15473133 - REVISED CABLE SEAL, CLOSED CAVITY 10; OPEN CAVITIES 12,13				249574	ADK	ADK	PD
15JAO4	R	06	-	-				15473133 - REVISED CABLE SEAL, CLOSED CAVITIES 12,13				250661	ADK	ADK	PD
31MR04	R	07	-	-				15491247 - RELEASED				253369	JPB	JAA	PD
09SE04	R	08	-	-				ALL PARTS - ADDED NOTES 5 & 6; 15476743 - REVISED CABLE SEAL, CLOSED CAVITY 18				258548	MLM	MLM	PD
21MR06	R	09	-	-				15480014 AND 15495462 - OBSOLETE				278493	JTZ	JAA	PD

DELPHI
DELPHI PACKARD ELECTRIC SYSTEMS
WARREN, OH

DR	DATE
APV01 J. VILLAMIL	25MR03
APV02 J. VILLAMIL	25MR03
APV03 PHIL DANCISON	25MR03
APV04	
APV05	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001

DRAWING NAME:
TAXI ASM CONN F MIC/P 100W SLD

DRAWING NUMBER:
15455459

SIZE: A0
SCALE: 2:1
FRAME NO: 1 OF 1
SHEET NO: 1 OF 1
REV: R 09

PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

DIMENSIONAL RANGE (MM)	TOLERANCE
FROM > 0 TO > 20	± 0.2
> 20 TO > 30	± 0.3
> 30 TO > 70	± 0.4
> 70 TO > 100	± 0.5
> 100 TO > 150	± 0.6
> 150 TO > 200	± 0.8
> 200 TO > 250	± 1.0
> 250 TO > 300	± 1.2
> 300 TO > 400	± 1.5

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15476593](#) [15475196](#)