











Bild 1: Crimpversion >1-2.5mm²
Picture 1: Crimp version

		D		D		D															
B	12	6 001 36 44	B	13609245	01	>1.0-2.5	□□□	0.8μm Au ⁷	3.6	1.8	3.8	4.7	2.6	4.9	1.5	3.3	5.8	19.2	3.0	0.4	
	11	6 001 44 42	---	---	---			3-5μm Ag													
	10	6 001 36 42	---	---	---			1.5-3 μm Ag													
	9	6 001 36 41	B	13609025	01			1-3μm Sn													
	8	6 001 36 34	B	13609247	01	0.5-1.0	□□	0.8μm Au ⁷	2.5	1.2	2.7	3.7	1.8	3.9	1.5	3.0	5.5	19.2	3.0	0.2	
	7	6 001 44 32	---	---	---			3-5μm Ag													
	6	6 001 36 32	---	---	---			1.5-3 μm Ag													
	5	6 001 36 31	B	13609027	01			1-3μm Sn													
A	4	6 001 36 14	B	13609246	01	0.2-0.35	□	0.8μm Au ⁷	1.9	0.8	1.9	2.5	1.0	2.5	1.7	2.5	5.3	18.8	3.4	0.2	
	3	6 001 44 12	---	---	---			3-5μm Ag													
	2	6 001 36 12	---	---	---			1.5-3μm Ag													
	1	6 001 36 11	B	13609026	01			1-3μm Sn													
	Pos.	Teile Nr. Part no.	Rev.	Delphi Teile Nr. Part no.	Rev.	Crimp- bereich Crimp zone (mm ²)	Crimp- code	Ober- flaeche Surface finish	B1 ±0.3	D1 ±0.3	(H1)	B2 ±0.3	D2 ±0.4	(H2)	A1 ±0.2	A2 ±0.2	A3 ±0.3	L1 ±0.5	L2 ±0.15	H3 +0.2	




BILD 2: Crimpversion 0.2-0.35mm²
Picture 2: Crimp version

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[60013631-L](#) [60013641-L](#)