










SYMBOL DEFINITION			MISSING NUMBERS
THE NUMBER INSIDE THE SYMBOL 	TOTAL NO. OF SYMBOLS ON DRAWING	11	
	LAST NO. USED	11	



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA. LIKE CAVITIES ARE IDENTICAL
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 12084449
SECONDARY TERMINAL LOCK 15356626
- MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 12064799

DELPHI Automotive Systems																																													
MATERIAL SPEC R0100113 PBT-GF 30-BLK		<table><tr><th colspan="6">DIMENSIONAL RANGE (MM)</th><th>CHART E</th></tr><tr><th>FROM</th><th>0</th><th>> 20</th><th>> 30</th><th>> 70</th><th>> 100</th><th></th></tr><tr><td>TO</td><td>20</td><td>30</td><td>70</td><td>100</td><td>> 100</td><td></td></tr><tr><td colspan="7">TOLERANCE UNLESS OTHERWISE SPECIFIED</td></tr><tr><td colspan="7">±0.15 ±0.2 ±0.3 ±0.4 ±0.5</td></tr><tr><td colspan="7">ANGULAR TOLERANCE ± 2°</td></tr></table>		DIMENSIONAL RANGE (MM)						CHART E	FROM	0	> 20	> 30	> 70	> 100		TO	20	30	70	100	> 100		TOLERANCE UNLESS OTHERWISE SPECIFIED							±0.15 ±0.2 ±0.3 ±0.4 ±0.5							ANGULAR TOLERANCE ± 2°						
DIMENSIONAL RANGE (MM)						CHART E																																							
FROM	0	> 20	> 30	> 70	> 100																																								
TO	20	30	70	100	> 100																																								
TOLERANCE UNLESS OTHERWISE SPECIFIED																																													
±0.15 ±0.2 ±0.3 ±0.4 ±0.5																																													
ANGULAR TOLERANCE ± 2°																																													
PART DRAWING				DISTR CODE																																									
CODE NUMBER 6901	DWG DATE 16DE98	SCALE 2:1																																											
QC SPEC	STYLE	VOLUME cm³ 6.135																																											
PART GEOMETRY 3D SOLID	UNLESS OTHERWISE SPECIFIED: PERFECT FORM REQUIRED FOR FEATURES OF SIZE AT MMC. TRUE POSITION TOLERANCES AND RELATED DATUMS APPLY AT CONDITION OF SIZE INDICATED IN FEATURE CONTROL FRAME. ALL OTHER GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. SEPARATE TRUE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.																																												
 CHANGE RESTRICTED NO MANUAL CHANGES	COPY OF MATH DATA DO NOT SCALE		REFERENCE 001,701	DATE 16DE98																																									
			DR D. HEBERLEIN	16DE98																																									
METRIC UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS	DRAWING NAME CONN 12M MIC/P 100		APVD1 D. HEBERLEIN	16DE98																																									
			APVD2 FRANCISCO KOPCA	26JA99																																									
			APVD3 PHILIP D. HELD	21DE98																																									
			APVD4																																										
			APVD5																																										
THIRD ANGLE PROJECTION 																																													
SHEET NUMBER 1 OF 1		DRAWING NUMBER 1535 6627		DWG STATUS STG REV N/P R 002 -	SIZE A2																																								

THE DIMENSION NUMBER(S) SHOWN BELOW
INDICATE DIMENSIONS THAT ARE PROCESS
SENSITIVE FOR PART PRODUCTION

10	11	
----	----	--

DIMENSIONS ENCLOSED IN () INDICATE
REFERENCE DIMENSIONS AND NO TOLERANCE
LIMITS ARE ESTABLISHED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15356627](#)