









F  
E  
D  
C  
B  
A



## CODINGS



DO NOT SCALE DRAWING		 <a href="http://www.fciconnect.com">www.fciconnect.com</a>	 ISO PROJECTION	SCALE 2:1
TITLE 6 way Duotwin to wire female Housing			DIMENSION IN MILLIMETERS	DWG SIZE A3
CATALOG NUMBER --			SHEET 1 of 1	
THIS DRAWING AND ALL OTHER INFORMATION CONTAINED THEREIN IS PROPRIETARY AND THE PROPERTY OF FCI.This drawing may not be copied, reproduced or disclosed to any third party without the expressed written permission of FCI.©FCI April 1999				

Direct Links

Cross Reference

RoHS/LF P/N search

Document & Drawing search

Application tooling

Services

Contact us

Distributor list

Pricing request

Order samples

Literature

Brochures & catalogs

Product documentation

Technical library

Start > Search=PPI0001083\* > PPI0001083

PPI0001083



PPI0001083

6 way DuoTwin to wire Female Housing

ACTIVE

Customer Drawing

Automotive division

Assistant Add to Favorites

Email Datasheet Print Datasheet

FCI Brings You More

- Contact our sales/technical support
- Sample request
- Price request

Specifications

General Mechanical Physical Terminal 1 Type Environmental Other Features

General

Application	Wire to Device
Ways	6
Coding version	A
Product Type	Housing
Coding	Yes
Family	Wire to Device
Features	6Way Female Housing
Hybrid	No

Main Terminal family	DuoTwin
Main Terminal size	0.64 mm
Sealed	No
Terminal Size	0.64
<b>Mechanical</b>	
Connector mating force	< 75N
<b>Physical</b>	
Color	Black
Material	PBT-GF15
Temperature (Range)	-40°C to+105°C
<b>Terminal 1 Type</b>	
Terminal type 1	DuoTwin Female 0.64 mm Terminal
Ways for Terminal Type 1	6
Contact insertion force for Terminal Type 1	< 5N
Contact Pitch for Terminal Type 1	2.54 mm
Retention force (Contact) for Terminal Type 1	> 60N
<b>Environmental</b>	
IMDS	Yes
<b>Other Features</b>	
Type	Female
Disclaimer	For more Information, please contact your local sales office. Displayed data is for information purposes only. The supply of some products might be limited to some customers.

Direct Links

Cross Reference  
RoHS/LF P/N search  
Document & Drawing search  
Application tooling

Services


Contact us  
Distributor list  
Pricing request  
Order samples

Literature

Brochures & catalogs  
Product documentation  
Technical library

Start > Search=PPI0001084\* > **PPI0001084**

**PPI0001084**



**PPI0001084**  
**6 way DuoTwin to wire Female Housing**  

ACTIVE

Customer Drawing

Automotive division

[Assistant](#) [Add to Favorites](#)  
  
[Email Datasheet](#) [Print Datasheet](#)  
  
**FCI Brings You More**  
[Contact our sales/technical support](#)  
[Sample request](#)  
[Price request](#)

Specifications

General Mechanical Physical Terminal 1 Type Environmental Other Features

<b>General</b>	
Application	Wire to Device
Ways	6
Coding version	B
Product Type	Housing
Coding	Yes
Family	Wire to Device
Features	6Way Female Housing
Hybrid	No

Main Terminal family	DuoTwin
Main Terminal size	0.64 mm
Sealed	No
Terminal Size	0.64
<b>Mechanical</b>	
Connector mating force	< 75N
<b>Physical</b>	
Color	Natural
Material	PBT-GF15
Temperature (Range)	-40°C to+105°C
<b>Terminal 1 Type</b>	
Terminal type 1	DuoTwin Female 0.64 mm Terminal
Ways for Terminal Type 1	6
Contact insertion force for Terminal Type 1	< 5N
Contact Pitch for Terminal Type 1	2.54 mm
Retention force (Contact) for Terminal Type 1	> 60N
<b>Environmental</b>	
IMDS	Yes
<b>Other Features</b>	
Type	Female
Disclaimer	For more Information, please contact your local sales office. Displayed data is for information purposes only. The supply of some products might be limited to some customers.

Direct Links

Cross Reference

RoHS/LF P/N search

Document & Drawing search

Application tooling

Services

Contact us

Distributor list

Pricing request

Order samples

Literature

Brochures & catalogs

Product documentation

Technical library

Start > Search=PPI0001087\* > PPI0001087

PPI0001087



PPI0001087

6 way DuoTwin to wire Female Housing

ACTIVE

Customer Drawing

Automotive division

Assistant Add to Favorites

Email Datasheet Print Datasheet

FCI Brings You More

- Contact our sales/technical support
- Sample request
- Price request

Specifications

General Mechanical Physical Terminal 1 Type Environmental Other Features

General

Application	Wire to Device
Ways	6
Coding version	Z
Product Type	Housing
Coding	Yes
Family	Wire to Device
Features	6Way Female Housing
Hybrid	No

Main Terminal family	DuoTwin
Main Terminal size	0.64 mm
Sealed	No
Terminal Size	0.64
<b>Mechanical</b>	
Connector mating force	< 75N
<b>Physical</b>	
Color	Water Blue
Material	PBT-GF15
Temperature (Range)	-40°C to+105°C
<b>Terminal 1 Type</b>	
Terminal type 1	DuoTwin Female 0.64 mm Terminal
Ways for Terminal Type 1	6
Contact insertion force for Terminal Type 1	< 5N
Contact Pitch for Terminal Type 1	2.54 mm
Retention force (Contact) for Terminal Type 1	> 60N
<b>Environmental</b>	
IMDS	Yes
<b>Other Features</b>	
Type	Female
Disclaimer	Displayed data is for information purposes only. For more Information, please contact your local sales office. The supply of some products might be limited to some customers.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[PPI0001083](#)