




SYMBOL DEFINITION					MISSING SYMBOLS					DWG STATUS				ZONE				REVISION HISTORY				AUTH	DR	CK	APV
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.					TOTAL NO OF INSPECTIONS REQUIRED	30	NO MISSING SYMBOL NUMBER	DATE	STG	REV	CHG	N/P	ALL ACTIVE PARTS - REDRAWN TO PD				207950				JGR	EDV	RC		
								09AP01	R	001	-	-													
					LAST NO. USED	30																			




CARRIER STRIP VIEW
TYPE 101




CARRIER STRIP VIEW
TYPE 102



CARRIER STRIP VIEW
TYPE 103




CARRIER STRIP VIEW
TYPE 104




TYPE 101

STAMP "CABLE I.D. NUMBER" ON UNDERSIDE IN THIS AREA WITH 1.2 HIGH CHARACTERS AS SPECIFIED IN CHART.




TYPE 102

STAMP "CABLE I.D. NUMBER" ON UNDERSIDE IN THIS AREA WITH 1.2 HIGH CHARACTERS AS SPECIFIED IN CHART.



TYPE 103

STAMP "CABLE I.D. NUMBER" ON UNDERSIDE IN THIS AREA WITH 1.2 HIGH CHARACTERS AS SPECIFIED IN CHART.






TYPE 104

STAMP "CABLE I.D. NUMBER" ON UNDERSIDE IN THIS AREA WITH 1.2 HIGH CHARACTERS AS SPECIFIED IN CHART.

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- VISIBLE CRACKS ARE NOT PERMISSIBLE.



12004431	R	CI	-	1.024 X 31.34	M1546284	12004439	R	CI	-	P1546284	104	8 - 5	6.46	9	6.7	10.2		
12004430	R	C	-	OBS	1.024 X 27.29	M1546283	12004438	R	CI	-	P1546283	103	8 - 5	6.46	9	6.7	10.2	
12004429	R	D1	-	1.024 X 31.34	S3614284	12004437	R	D1	-	P3614284	104	3	4.67	12	5.6	8.2		
12004428	R	D	-	OBS	1.024 X 27.79	S3614283	12004436	R	D1	-	P3614283	103	3	4.67	12	5.6	8.2	
12004427	R	E	-	OBS	0.724 X 28.58	M3614381	12004435	R	E1	-	P3614381	102	2 - 1	3.97	15	4.2	6	
12004426	R	E	-	OBS	0.724 X 25.81	M3614380	12004434	R	E1	-	P3614380	101	2 - 1	3.97	15	4.2	6	
12004425	R	E1	-	0.645 X 28.58	M3614379	12004433	R	E1	-	P3614379	102	0.8 - 0.5	3.13	19	3.6	5.1		
12004424	R	E	-	OBS	0.645 X 25.81	M3614378	12004432	R	E1	-	P3614378	101	0.8 - 0.5	3.13	19	3.6	5.1	
PART NO	STG	REV	N/P	STATUS	MAT'L	SIZE	SPEC	PART NO	STG	REV	N/P	STATUS	SPEC	TYPE	SIZE (MM²)	MAX DIA	I.D.	
UNPLATED							TIN PLATED							CABLE				
														E ±0.4				F ±0.4

(6) PROCESS SENSITIVE DIMENSION			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)	FROM	TO	CHART 0
0	0	> 12	
TOLERANCE UNLESS OTHERWISE SPECIFIED	±0.15	±0.3	
ANGULAR TOLERANCE	± 2°		

DELPHI Automotive Systems			
MATERIAL SPEC SEE CHART			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI - A 10949001			
PART DRAWING			DISTR CODE
CODE NUMBER 6900	DWG DATE 17AU76	SCALE 2:1	D
OC SPEC	STYLE	VOLUME cm³	
PART GEOMETRY 3D SOLID	UNLESS OTHERWISE SPECIFIED: THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M - 1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.		
COPY OF MATH DATA DO NOT SCALE	REFERENCE	DR	DATE
	APVD1 R.D. WALLACE		17AU76
METRIC UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS	APVD2 T. MUDREY		20AU76
	APVD3 R.D. KEARNS		010C76
THIRD ANGLE PROJECTION		DRAWING NAME	
TERM RING STROTH			
SHEET NUMBER 1 OF 3	DRAWING NUMBER 12004423	DWG STATUS R 001	SIZE A0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12004435](#) [12004437](#) [12004438](#) [12004439](#)