


| 6            | 5        |     |
|--------------|----------|-----|
| $6.6^{+0.2}$ | VIEW D-D | VIE |
| VIEW B-B     |          |     |




CORE WINGS BLANK

SUPPLIER IDENT.

TYPE 1

6



TYPE 2


NOTE:

- MARK:


|     | 0.38x26 |                             | SILVER PLATING  | > 4.0-6.0  | 6         | 4.3   |     | 5.4  | 5.8                  | 4.9               | 6.0     |     |  |
|-----|---------|-----------------------------|-----------------|------------|-----------|---|-----|------|----------------------|-------------------|---------|-----|--|
|     | 0.38x26 | M3677802<br>PHOSPHOR BRONZE |                 | > 2.5-4.0  | 4         | 3.7   | 1   | 4.4  | 5.6                  | 4.6               | 5.5     |     |  |
|     | 0.38x26 |                             |                 | > 1.0-2.5  | 2.5       | 3.0   |     | 3.4  | 5                    | 4.0               | 5.3     |     |  |
|     | 0.38x26 |                             |                 | 0.5-1.0    | 1         | 2.1   | 2   | 2.8  | 4.2                  | 3.0               | 4.4     |     |  |
|     | 0.38x26 |                             |                 | > 4.0-6.0  | 6         | 4.3   | 1   | 5.4  | 5.8                  | 4.9               | 6.0     |     |  |
|     | 0.38x26 | M1401802                    |                 | > 2.5-4.0  | 4         | 3.7   |     | 4.4  | 5.6                  | 4.6               | 5.5     |     |  |
| . — | 0.38x26 | BRASS                       | SILVER PLATING  | > 1.0-2.5  | 2.5       | 3.0   |     | 3.4  | 5                    | 4.0               | 5.3     |     |  |
|     | 0.38x26 |                             |                 | 0.5-1.0    | 1         | 2.1   | 2   | 2.8  | 4.2                  | 3.0               | 4.4     |     |  |
| . — | 0.38x26 |                             |                 | > 4.0-6.0  | 6         | 4.3   | 1   | 5.4  | 5.8                  | 4.9               | 6.0     |     |  |
|     | 0.38x26 |                             |                 | > 2.5-4.0  | 4         | 3.7   |     | 4.4  | 5.6                  | 4.6               | 5.5     |     |  |
|     | 0.38x26 | PHOSPHOR BRONZE             |                 | > 1.0-2.5  | 2.5       | 3.0   |     | 3.4  | 5                    | 4.0               | 5.3     |     |  |
|     | 0.38x26 |                             |                 | 0.5-1.0    | 1         | 2.1   | 2   | 2.8  | 4.2                  | 3.0               | 4.4     |     |  |
| . — | 0.38x26 |                             |                 | > 4.0-6.0  | 6         | 4.3   |     | 5.4  | 5.8                  | 4.9               | 6.0     |     |  |
|     | 0.38x26 | M3677802<br>PHOSPHOR BRONZE |                 | > 2.5-4.0  | 4         | 3.7   | 1   | 4.4  | 5.6                  | 4.6               | 5.5     |     |  |
|     | 0.38x26 |                             | PHOSPHOR BRONZE |            | > 1.0-2.5 | 2.5   | 3.0 |      | 3.4                  | 5                 | 4.0     | 5.3 |  |
|     | 0.38x26 |                             |                 | 0.5-1.0    | 1         | 2.1   | 2   | 2.8  | 4.2                  | 3.0               | 4.4     |     |  |
| . — | 0.38x26 |                             |                 | > 4.0-6.0  | 6         | 4.3   |     | 5.4  | 5.8                  | 4.9               | 6.0     |     |  |
|     | 0.38x26 | M3713802                    |                 | > 2.5-4.0  | 4         | 3.7   | 1   | 4.4  | 5.6                  | 4.6               | 5.5     |     |  |
|     | 0.38x26 | BRASS<br>TIN PLATING        |                 | > 1.0-2.5  | 2.5       | 3.0   |     | 3.4  | 5                    | 4.0               | 5.3     |     |  |
|     | 0.38x26 |                             |                 | 0.5-1.0    | 1         | 2.1   | 2   | 2.8  | 4.2                  | 3.0               | 4.4     |     |  |
| - — | 0.38x26 |                             |                 | > 4.0-6.0  | 6         | 4.3   |     | 5.4  | 5.8                  | 4.9               | 6.0     | NS  |  |
|     | 0.38x26 | M1401802                    | M1401802        |            | > 2.5-4.0 | 4   | 3.7 | 1    | 4.4                  | 5.6               | 4.6     | 5.5 |  |
|     | 0.38x26 | BRASS                       |                 | > 1.0-2.5  | 2.5       | 3.0   |     | 3.4  | 5                    | 4.0               | 5.3     |     |  |
|     | 0.38x26 | BRASS                       |                 | 0.5-1.0    | 1         | 2.1   | 2   | 2.8  | 4.2                  | 3.0               | 4.4     |     |  |
|     | MAT'L   |                             |                 | SIZE (mm2) |           | $\begin{array}{c ccccccccccccccccccccccccccccccccccc$ |     |      |                      |                   |         |     |  |
| JS  | SIZE    | MAT'L SPEC                  | POS PLATING     |            | TYPE      | ]   |     |      |                      |                   |         |     |  |
|     |         |                             |                 | UADEE      |           |   |     |      |                      |                   |         |     |  |
|     |         |                             |                 |            |           |   |     |      | ATE REFEF<br>NO TOLE | RENCE DI<br>RANCE | MENSION |     |  |
|     |         |                             |                 |            |           |   |     | TOLE | ERANCE L             | JNLESS            |         |     |  |

5

| 4 |                                       |            |     | 3   |     |      |        |          |
|---|---------------------------------------|------------|-----|-----|-----|------|--------|----------|
|   | D'                                    | DWG STATUS |     |     |     |      |        |          |
|   | DATE                                  | STG        | REV | CHG | N/P | ZONE |        |          |
|   | 29SE03                                | -          | 001 | -   | Ι   |      | ΤΑΧΙ ν | VAS 1543 |
|   |                                       |            |     |     |     |      |        |          |
|   |                                       |            |     |     |     |      |        |          |
|   |                                       |            |     |     |     |      |        |          |
|   | · · · · · · · · · · · · · · · · · · · |            |     |     |     |      |        |          |



EW E-E



 $(\oplus)$ 

2

 $\sim$ 

DRAWING NUMBER

OF

## SUPPLIER IDENTIFICATION CABLE SIZE IDENTIFICATION

SHEET NUMBER DECIMAL: ANGULAR: ±2° ONE PLACE ±0.3 TWO PLACE ±0.15

4

|       |                 | 2   |                            |       |                     |                 | 1    |              |      |
|-------|-----------------|---|----------------------------|-------|---------------------|-----------------|------|--------------|------|
|       |                 | REVISION HIS                                | STORY                      |       |                     | AUTH            | DR   | ск           | APVD |
| ΤΑΧΙ  | WAS 15438       | 3754  |                            |       |                     |                 | РОТ  | AIM          | ASG  |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
|       |                 |   |                            |       |                     |                 |      |              |      |
| AND   | RECYC           | LED CONTEI                                  | NT PER D                   | ELPł  | H-A 1094            | <u> </u>        | RCOD | E            |      |
| PAF   | RT DF           | RAWING                                      | <b>)</b>                   |       |                     |                 |      |              |      |
|       | 'G DATE<br>MY94 |   |                            | SCAL  | E<br>IOT SCAL       | E               |      |              |      |
| ST    | YLE             |   |                            | VOLU  | VIE cm <sup>3</sup> |                 |      |              |      |
|       |                 | UNLES                                       | S OTHERWI                  | SE SF | PECIFIED:           |                 |      |              |      |
|       |                 | IENT IS IN ACC                              | ORDANCE                    | WITH  | ASME Y14            |                 | 1    |              |      |
| TO    | _ERANCIN        | D BY THE GM (<br>NG ADDENDUN<br>D DATUMS AP | <mark>1 - 1997</mark> . AL | L GE  | DMETRIC T           | OLERAN          |      |              |      |
| MM    | C) DOES I       | NOT APPLY WH                                | IEN RELATI                 | ONSH  | IP BETWEE           | EN FEATUR       | RES  |              |      |
| SEF   | PARATE P        | OSITION CALL                                | DUTS MAY E                 | BE GA |                     |                 |      |              |      |
|       | FERENCE         |   | DR                         |       | <u></u>             |                 |      | DAT          |      |
|       |                 |   |                            |       | CHINI               |                 |      | 9SE(<br>9SE( |      |
|       |                 |   |                            |       |                     |                 |      | 95E0<br>95E0 |      |
|       |                 |   |                            | ROPF  |                     |                 |      | 9SE0         |      |
|       |                 |   | APVD4                      |       |                     |                 |      |              |      |
|       |                 |   | APVD5                      |       |                     |                 |      |              |      |
|       | AWING NA        |   | ΝΛΙΝΙΔΙ Γ                  | = =1  | ላጊ ይ ሪካ             | nm              |      |              |      |
|       |                 |   |                            |       |                     |                 | i    |              |      |
| JMBEF |                 |   |                            |       | i                   | STATUS<br>REV N | /P   | siz          |      |
| 15    | 44              | 6846  |                            |       | - (                 | 001             |      | A            | 2    |
|       |                 | 2   |                            |       |                     | I               | 1    |              |      |

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

<u>Aptiv:</u> 15327331