



15383048 & 12160811  
PLATING LOCATION DETAIL




12110502  
PLATING LOCATION DETAIL



THIS WIDTH MUST BE MAINTAINED FOR  
A MINIMUM DISTANCE OF 8.8 FROM THE  
FRONT OF THE BOX TO THE BACK OF  
THE STOP TO LOCK FEATURE

TYPE 101

STAMP I.D. "PXX" IN THIS AREA (0.6)  
CHARACTERS XX DESIGNATES DIE NUMBER  
LOCATION IS APPROXIMATE.



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:  
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND  
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION  
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL  
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL  
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. REFERENCE MATING COMPONENTS OR EQUIVALENT:  
TERMINAL 12047767
3. NO CHANGE IS TO BE MADE TO THIS PART WITHOUT  
IFG AUTORIZATION (P/N 12110502 ONLY).

15383048	01	AH		0.381 X 34.52	TIN BRASS ALLOY GOLD, TIN & NICKEL ELECTROPLATE	0.35- 0.5	21	2.4-1.47	301	2.4
12160811	C9	-		0.381 X 34.52	TIN BRASS ALLOY GOLD, TIN & NICKEL ELECTROPLATE	0.5 - 0.8	19	2.4-1.84	301	3.2
12110502	D9	-		0.381 X 34.52	TIN BRASS ALLOY GOLD, TIN & NICKEL ELECTROPLATE	0.5 - 0.8	19	2.4-1.84	301	3.2
PART NO	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC	SIZE (MM²)	ID	DIA	TYPE	
PLATED						CABLE				

PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART D
FROM 0 TO 12	> 12
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.1	±0.2
ANGULAR TOLERANCE ±2°	

DWG TYPE PART DRAWING	
STYLE	
VOLUME (CNP)	DISTR CODE D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2003 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	NX

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH	
DR	DATE
APVD1 H. CASTRILLON	08MY97
APVD2 J. VAZQUEZ	12MY97
APVD3 R. LANDRIES	12MY97
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHART	
DRAWING NAME TAXI TERM M M/P 150	
DRAWING NUMBER 12040995	
SIZE A1	SCALE 10:1
FRAME NO 1 OF 1	SHEET NO 3 OF 3
STS R	REV 10
N/P -	

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	6
	LAST NO. USED	6

MISSING SYMBOLS	
NO MISSING SYMBOL NUMBER	

DWG STATUS					ZONE	REVISION HISTORY		AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG							
30N099	R	01	-	-		ALL PARTS - REDRAWN TO PD		196871	GMC	GMC	OG
30N099	R	02	-	-		15383048 - RELEASED		990005	GMC	GMC	OG
19N003	R	03	-	-		ALL PARTS - UPDATED CHART "G" WAS "A"		247796	LOA	FKV	RD
10N004	-	04	-	-		ALL PARTS - UPDATED MAT'L SPEC CALLOUT		261173	JS	JS	BG
30MR05	R	05	-	-		ALL PARTS - TOLERANCE ON DIM #5 WAS ±0.1		265258	LMB	LMB	MM
16AU05	R	06	-	-		ALL PARTS - ADDED STAMP I.D. LABEL		270616	RTV	FRG	MKM
15JA09	R	07	-	-		ALL ACTIVE PARTS - ADDED LABEL AND DIM 2.5 +0.1/-0.15 WAS 2.5 ±0.1		407112	SCR	ECB	GEM
10DE09	R	08	-	-		ALL PARTS - REFERENCE MATING TERMINAL WAS 12047776		409633	DGL	DGL	GEM
31MY10	R	09	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES		410934	MAB	JAA	GEM
21JL10	R	10	-	-		ALL PARTS - ADDED PLATING INFORMATION		411388	AHY	DMC	GEM

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12110502-L](#)