










MISSING SYMBOLS	DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	AP/OP/CD	
	DATE	STG	REV	N/P	CHG					1	2
NO MISSING SYMBOL NUMBER	26.J06	R	01	-	-	13959247 - RELEASED: 12160280 - WAS SEPARATE DWG	282764	RWG	JVM	CSD	
	22AU06	R	02	-	-	ALL PARTS - CONNECTOR WAS 12146395 IN NOTE 4, SECONDARY TERMINAL LOCK WAS 12110746 AND CONDUIT CLIP WAS 12110724 IN NOTE 5	283835	JTZ	JVM	CSD	
	18JA07	R	03	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	400105	CCV	FRB	CSD	
	07.A07	R	04	-	-	ALL PARTS - ADDED NOTE 7	401613	PCP	PCP	CSD	



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



- | | | | |
|--|--|---|--|
| DWG TYPE | | PART DRAWING | |
| STYLE | | | |
| VOLUME (CM3)
SEE CHART | | DISTR CODE
D | |
| UNLESS OTHERWISE SPECIFIED
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
AND AMENDED BY THE ASME Y14.5M-2001. SEPARATE PATTERNS OF
FEATURES MAY BE ISSUED SEPARATELY, REGARDLESS OF DATUM
REFERENCES. | | | |
| ALL DIMENSIONS ARE IN MILLIMETERS | | | |
| REFERENCE | | | |
| THIRD ANGLE
PROJECTION | | DO NOT
SCALE | |
| USE MATH DATA | |   | |
|   | | | |

DELPHI										
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH										
DR					DATE					
AP/01 RICARDO MARTINEZ					26 JUL 06					
AP/02 J. VILLAMIL					21 JUL 06					
AP/03 CHR. PROFIO					09AUG06					
AP/04										
AP/05										
SUBSTANCES OF CONCERN AND RECYCLED CONTENT FROM DELPHI 10949301										
MATERIAL SER. CHART										
DRAWING NAME TAXI CONN F MIC/P 100W SLD										
DRAWING NUMBER 13595416										
SIZE A0		SCALE 2:1		FRAME NO 1 OF 1		SHEET NO 1 OF 1		STS R 04		N/P -

13595247	01	AC		M4695003 PBT HS 1M GRA	102	13.295
12160280	A7	-		M3592025 PA66 HS GRA MD	101	13.295
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	TYPE	VOL (CM ³)

		1		PROCESS SENSITIVE DIMENSIONS				
		DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NOT TOLERANCE LIMITS ARE ESTABLISHED						
DIMENSIONAL RANGE (MM)		CHART						
FROM	TO	> 0	> 30	> 100	> 150	> 200	> 250	> 300
		0	30	100	150	200	250	300
		TOLERANCE UNLESS OTHERWISE SPECIFIED						
		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8
		ANGULAR TOLERANCE ±2°						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12160280](#)