




NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
- DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. TERMINAL ENGAGE 3N TO 10N TERMINAL DISENGAGE 2N TO 8N WHEN MATED TO A 0.81 THICK X 1.5 WIDE HARDENED STEEL BLADE.
3. RECOMMENDED MATING BLADE:
WIDTH :1.5
THICKNESS :0.825 ±0.035
LENGTH :7

					0.254 X 29.36		12110236	D3			COPPER ALLOY	1 - 0.8 - 0.5	2.4 - 2.03	60	3
PART NO	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	STATUS	MAT'L SPEC	SIZE (MM²)	DIA	ID	G±0.2	
UNPLATED						PLATED						CABLE			

5		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART D	
FROM	0	>12	
TO	12		
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.1		±0.2	
ANGULAR TOLERANCE ±2°			

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CNP)		DISTR CODE	
		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
			
		USE MATH DATA	
			

DELPHI				
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH				
DR			DATE	
APVD1	JOSE LUIS TAPIA		22SE04	
APVD2	FRANCISCO KOPCA		22SE04	
APVD3	BRIAN GROUBERT		24SE04	
APVD4				
APVD5				
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001				
MATERIAL SEE CHART				
DRAWING NAME				
TAXI TERM F M/P 150 TANG				
DRAWING NUMBER				
12085010				
SIZE	SCALE	FRAME NO	SHEET NO	STG
A1	20:1	1 OF 1	1 OF 1	R
				REV 03
				N/P -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12110236-L](#)